

## Genuine Canon Inks

With a Canon PIXMA, ink is the lifeblood of everything you create. It can make the difference between dull or vibrant colours, between blurry or sharp photo prints, and between prints that fade easily or those that last a lifetime.

If you never want to compromise on quality, only genuine Canon inks guarantee the performance levels you expect from your PIXMA.

Genuine Canon inks have been developed to remain stable when heated to high temperatures. And to form microscopic ink droplets – two million times smaller than a raindrop – that remain spherical for precise placement on paper.

Only genuine Canon inks have been specifically designed and developed to meet these exacting standards, print after print.



| INK                     | MX360 | MX410 | MX420 | MX885 | IX6550 | IX7000 | iP100 |
|-------------------------|-------|-------|-------|-------|--------|--------|-------|
| PG-510 Black            | ●     | ●     | ●     |       |        |        |       |
| CL-511 Colour           | ●     | ●     | ●     |       |        |        |       |
| CL-511 ChromaLife Pack  |       |       | ▶     |       |        |        |       |
| PG-512 Black            | ▶     | ▶     | ▶     |       |        |        |       |
| CL-513 Colour           | ▶     | ▶     | ▶     |       |        |        |       |
| PGI-525PGBK             |       |       |       | ●     | ●      |        |       |
| PGI-525PGBK Twin Pack   |       |       |       | ▶     | ▶      |        |       |
| CLI-526BK               |       |       |       | ●     | ●      |        |       |
| CLI-526C                |       |       |       | ●     | ●      |        |       |
| CLI-526M                |       |       |       | ●     | ●      |        |       |
| CLI-526Y                |       |       |       | ●     | ●      |        |       |
| CLI-526 C/M/Y Multipack |       |       |       | ▶     | ▶      |        |       |
| PGI-9PGBK               |       |       |       |       |        | ●      |       |
| PGI-9C                  |       |       |       |       |        | ●      |       |
| PGI-9M                  |       |       |       |       |        | ●      |       |
| PGI-9Y                  |       |       |       |       |        | ●      |       |
| PGI-7BK                 |       |       |       |       |        | ●      |       |
| PGI-9 Clear             |       |       |       |       |        | ●      |       |
| PGI-35 Black            |       |       |       |       |        |        | ●     |
| CLI-36 Color            |       |       |       |       |        |        | ●     |
| CLI-36 ChromaLife Pack  |       |       |       |       |        |        | ▶     |

● Compatible  
▶ Optional compatible cartridge, which does not come in the product box.



PIXMA offers a suite of software that makes it easier than ever to get efficient.



### MP Navigator EX

Allows you to easily convert documents to text files or searchable PDFs, complete with password protection to safeguard any confidential information.




### Easy-PhotoPrint EX

Photo printing has never been simpler thanks to Easy-PhotoPrint EX, offering features such as red-eye correction, and face smoothing.



### Auto Document Fix

Auto Document Fix enhances the quality and legibility of scans by making intelligent automatic adjustments to every page.



### Easy-WebPrint EX

Content from multiple websites can be effortlessly combined and printed with Easy-WebPrint EX.



### Full HD Movie Print Feature

Turn your Canon digital camera movie moments into beautiful prints with Canon's Full HD Movie Print feature.



### Fax

Featuring high-speed "Super G3" Colour FAX.



### Fine cartridges

The integration of print head and ink tank realizes downsizing of printer body and replacement of print head and ink tank at a time.



### Wi-Fi

Easy to setup wireless LAN allows you to share print and scan features among multiple PCs.



### Ethernet

Ethernet connectivity allows you to share print and scan features among multiple PCs.



### Dual Function Panel

Dual Function Panel provides easy-to-follow operation with flexible key assignment, and enlarged easily recognisable keys.



### Auto Duplex print

Automatically print on both sides of the paper.



### Duplex ADF

Allows automatic scanning, copying and faxing of multi-page double-sided documents.



### 9600 dpi

The high density print head enables high-resolution printing.



### 1pl

High-density FINE print head technology is capable of ejecting microscopic ink droplets as small as 1 pl (one trillionth of a litre).



### 5 single inks

On-screen messages tells users how much ink is remaining. LED on ink tanks blinks on when the ink is running out. These features enhance the convenience of use.



### PgR

Achieves both superior photo print quality on plain paper, and print durability / water-fastness.



### Lucia Ink

Pigment-based LUCIA ink maintain the longevity of printouts.



### A3+

Supports various sizes up to A3+ size.



### ChromaLife 100+

A combination of genuine dye-based ink and genuine photo paper provides more vibrant, beautiful and longer lasting photos.

For full specifications see [www.canon-europe.com](http://www.canon-europe.com)

| AVAILABLE FUNCTIONS                              | PIXMA MX360                | PIXMA MX410<br>PIXMA MX420                         | PIXMA MX885                                        | PIXMA iX6550                | PIXMA iX7000                                                                     | PIXMA iP100<br>PIXMA iP100mb                |
|--------------------------------------------------|----------------------------|----------------------------------------------------|----------------------------------------------------|-----------------------------|----------------------------------------------------------------------------------|---------------------------------------------|
| PRINT RESOLUTION / DROPLET SIZE MIN.             | Up to 4800 x 200 dpi / 2pl | Up to 4800 x 200 dpi / 2pl                         | Up to 9600 x 2400 dpi / 1pl                        | Up to 9600 x 2400 dpi / 1pl | Up to 4800 x 1200 dpi / 2pl                                                      | Up to 9600 x 2400 dpi / 1pl                 |
| PHOTO LAB QUALITY SPEED BORDERLESS 10X15CM (STD) | Approx. 43 seconds         | Approx. 42 seconds                                 | Approx. 20 seconds                                 | Approx. 36 seconds          | Approx. 44 seconds                                                               | Approx. 50 seconds                          |
| MONO / COLOUR PRINT SPEED ISO-ESAT A4 DOCUMENT   | Approx. 8.4 ipm / 4.8 ipm  | Approx. 8.7 ipm / 5.0 ipm                          | Approx. 12.5 ipm / 9.3 ipm                         | Approx. 11.3 ipm / 8.8 ipm  | Approx. 10.2 ipm / 8.1 ipm                                                       | Approx. 9.0 ipm / 5.9 ipm                   |
| COPY SPEED COLOUR A4 DOCUMENT 55x11 / 54x11      | Approx. 4.0 ipm / 2.9 sec. | Approx. 4.0 ipm / 2.3 sec.                         | Approx. 7.4 ipm / 1.5 sec.                         | -                           | -                                                                                | -                                           |
| PAPER INPUT                                      | Rear Tray: Max. 100 sheets | Rear Tray: Max. 100 sheets                         | Rear Tray: Max. 150 sheets<br>Cassette: 150 Sheets | Rear Tray: Max. 150 sheets  | Rear Tray: Max. 20 sheets<br>Cassette: Max. 250 sheets<br>Manual feed: 10 sheets | Rear Tray: Max. 50 sheets                   |
| TWO SIDED PRINTING                               | Manual                     | Manual                                             | Automatic                                          | Manual                      | Automatic                                                                        | Manual                                      |
| CONNECTIVITY                                     | USB                        | USB, BLUETOOTH (optional), Wi-Fi, Ethernet (MX420) | USB, BLUETOOTH (optional), Wi-Fi, Ethernet         | USB                         | USB, Ethernet                                                                    | USB, iFDD, BLUETOOTH (optional), PictBridge |
| DISPLAY                                          | Full Dot LCD               | Full Dot LCD (MX410)<br>6.2cm Colour TFT (MX420)   | 7.5cm Colour TFT and Dual Function Panel           | -                           | -                                                                                | -                                           |
| AUTO DOCUMENT FEEDER                             | ✓                          | ✓                                                  | ✓ Duplex                                           | -                           | -                                                                                | -                                           |
| DIMENSIONS (W X D X H)                           | 458 x 415 x 198mm          | 458 x 415 x 198mm                                  | 491 x 448 x 218mm                                  | 549 x 299 x 159mm           | 647 x 519 x 260mm                                                                | 322 x 185 x 61.7mm (without battery)        |
| WEIGHT                                           | Approx. 8.5kg              | Approx. 8.6kg / 8.9kg                              | Approx. 11.7kg                                     | Approx. 7.6kg               | Approx. 19.9kg                                                                   | Approx. 2.0kg (without battery)             |

Step through the range PIXMA for Work

▶ A handy arrow helps you instantly identify a feature that is improved compared to the preceding model in the same category.



Stylish practicality.

PIXMA for Work Range Guide.

you can



Canon

Style and practicality are expertly matched in our new range of PIXMAs. Offering outstanding quality prints these productive and beautifully designed devices are a pleasure to work with – wherever you choose to be.



## PIXMA MX360\*

The All-In-One that handles everything with ease.



Print, copy, scan and fax for the home and office

Quality prints at up to 4800 x 1200 dpi with min. 2pl ink droplets

Fully integrated 30 sheet Auto Document Feeder for fast scan, copy, and fax of large documents

ISO ESAT 8.4 ipm mono / 4.8 ipm colour print speed plus Quick Start

Print 10x15cm borderless photos in approx. 43 seconds

\* not available in the UK



Scan PDFs and JPEGs straight to USB memory – without a PC

Precise control of web printing with Easy-WebPrint EX

Enhance legibility of scanned documents with Auto Document Fix

Print quality photos from movies captured on select Canon cameras with Full HD Movie Print

PictBridge for direct camera connection

## PIXMA MX410

The Wi-Fi All-In-One that handles everything with ease.



Print, copy, scan, and fax from anywhere in the home or office with built-in Wi-Fi

Sleek and stylish all-black design

Quality prints at up to 4800 x 1200 dpi with min. 2pl ink droplets

Fully integrated 30 sheet Auto Document Feeder for fast scan, copy, and fax of large documents

Efficient ISO ESAT 8.7 ipm mono / 5.0 ipm colour print speed plus Quick Start



Print 10x15 cm borderless photos in approx. 42 seconds


Scan PDFs and JPEGs straight to USB memory – without a PC

Precise control of web printing with Easy-WebPrint EX

Print quality photos from movies captured on select Canon cameras with Full HD Movie Print

## PIXMA MX420

The stylish All-In-One for the home office.



Print, copy, scan, and fax from anywhere with built-in Wi-Fi and Ethernet

Sleek and stylish all-black design

Easy operation via a 6.2cm colour TFT display

Quality prints at up to 4800 x 1200 dpi with min. 2pl ink droplets

Fully integrated 30 sheet Auto Document Feeder for fast scan, copy, and fax of large documents



Efficient ISO ESAT 8.7 ipm mono / 5.0 ipm colour print speed plus Quick Start

Print 10x15 cm borderless photos in 42 seconds


Save scans and faxes straight to USB or memory card without a PC

Precise control of web printing with Easy-WebPrint EX

Print quality photos from movies captured on select Canon cameras with Full HD Movie Print

## PIXMA MX885

Quality, speed and simplicity in one powerful All-In-One.



Print, copy, scan, and fax from anywhere in the office with built-in Wi-Fi and Ethernet

Sleek and stylish black design

Easy operation with Dual Function Panel and 7.5 cm colour TFT display

35-sheet Duplex Auto Document Feeder for scan, copy, fax of two-sided documents

Productive ISO ESAT 12.5 ipm mono / 9.3 ipm col. print speed plus Quick Start



5 Single Ink tanks to minimise waste

Photolab-quality at up to 9600 dpi print resolution and min. 1pl droplet size


Print 10x15 cm borderless photos in approx. 20 sec.

Intuitive software for photo and document scanning and printing

Save scans and faxes straight to USB or memory card – without a PC

## PIXMA iX6550

Compact and stylish A3+ printer for photos and documents.



Ultra compact and stylish A3+ printer ideal for home or small offices

Photolab-quality prints with min. 1pl ink droplets and up to 9600 dpi

5 Single Ink Tanks minimise waste and print costs

Efficient document print speeds - ISO ESAT 11.3 ipm for black and 8.8 ipm for colour

Print high quality 10x15 cm borderless photos in approx. 36 seconds



Create professional marketing materials with "Solution Templates"

Print quality photos from movies captured on select Canon cameras with Full HD Movie Print

Efficient web printing with Easy-WebPrint EX

Access exclusive professional content with CREATIVE PARK PREMIUM

ChromaLife100\* for long lasting beautiful photos

## PIXMA iX7000

The A3 document and photo printer that's perfect for small businesses and offices.



Ultimate A3 inkjet printer for business with superior plain paper printing and long-lasting photo printing up to A3+

Canon uses ISO standard for realistic print speeds, document ESAT speed 10.2ipm mono, 8.1ipm colour

4800x1200dpi 2pl with Pgr Technology and Lucia pigment inks: 10x15cm borderless photo in approx. 44sec



High capacity 250-sheet lower paper cassette, manual feed tray and rear tray for versatile high capacity paper input

Up to A3 auto duplex print

Printer sharing via built-in Ethernet

Download Solution Templates for MS Word to easily create posters and flyers

Easy-PhotoPrint Pro plug-in for Elements & Photoshop

## PIXMA iP100

with and without battery

Precision photo and document printing wherever you are.



Compact and portable document and photo printer

9600 x 2400 dpi FINE print head with 1pl

5 ink system with Photo Black ink for enhanced photo quality

Borderless 10 x 15 photo prints in approx. 50 sec.

ChromaLife100 for long-lasting, beautiful photos



ISO Standard Speed: 9.0 IPM Mono / 5.9 IPM Colour ESAT

Pigment Black ink for crisp and sharp text

Stylish silver finish with piano black panel detail

Optional accessories include rechargeable battery, Bluetooth® adaptor and in-car charger

Printing freedom with IrDA IR or optional Bluetooth®

With the optional rechargeable battery (standard with iP100wb), the iP100 delivers the ultimate in convenient, portable photo and document printing. Connect via the standard IrDA infrared or an optional Bluetooth adaptor and get speedy document or photo prints on the move.

In-car charger (PU-200U)



Battery (LK-62)\*



Bluetooth Adapter (BU-30)



\* Optional battery (LK-62) is included in iP100wb

Canon

Canon Inc.  
canon.com

Canon Europe  
canon-europe.com

Canon Europe Ltd  
3 The Square, Stockley Park  
Uxbridge, Middlesex  
UB11 1ET UK

English Edition 0150W584  
© Canon Europa N.V., 2011