




Specifications:

- Voltage rating: 16 VDC
- Current rating: .3A
- Contact resistance: 30m Ω
- Insulation resistance: 100M Ω 500 VDC
- Dielectric: strength: 500VAC 1 min.

Material:

- Contacts: phosphor bronze
- Housing: nylon-46 G30% UL94V0 black

Mechanical:

- Durability: 5000 cycles
- Insertion force: .3 Kg to 2.0 Kg
- Extraction force: .2Kg to 2.0 Kg
- Soldering temperature: 260°C for 5 seconds
- Operating temperature: -25 to 80°C

Plating:

- Contacts: gold flash

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2623/TR-E](#)