


Sales Outline Drawing**Revision A****Specifications:**

Oscillation Frequency (Hz)	Multiple
Operating Voltage (Vdc)	9 - 48
Current Consumption (mA/max)	3 at 9Vdc, 5 at 12VDC, 20 at 40Vdc, 25 at 48Vdc
Sound Pressure Level at 1 foot at Rated Voltage (dB/min)	72 at 9VDC, 75 at 12Vdc, 79 at 40Vdc, 80 at 48Vdc
Tone/Pulse Rate (Hz0)	Constant
Operating Temperature (°C)	-20 ~ +65
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	23
Condition by wave soldering (°C)	245 ±5 / 3±0.5 sec
Condition by hand soldering (°C)	350 ±20 / within 5 sec
Options	For other options contact factory

RoHS Compliant**Dimensions:** (units: mm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PK-27A29ERB481Q](#)