


1

2

3

4




A

A

B

B



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.GX00
15	39.14	33.32	25.18	24.54	19.18	D15S24A.GX00
25	53.03	47.04	39.12	38.25	33.12	D25S24A.GX00
37	69.32	63.50	55.68	54.71	49.68	D37S24A.GX00

C

C

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.GX00LF


D

D

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

rev	ecn no	dr	date
B	-	JAR	1999/10/18
D	LS05-001	MPE	2005/03/14
E	LS05-0056	MPE	2005/06/28
F	LS06-0019	LGO	2006/02/07
G	LS06-0097	LGO	2006/07/28
H	110-0059	NG	2010-02-23
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)

European Views

www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406 ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED		SPECIFIED		mm	
Dr	JOUBERT	1996/09/10	ANGULAR	0.X	±0.1	size	A3
Eng	PESSON	1996/09/10	LINEAR	0.XX	±0.1	size	A3
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±0.1	ECN	110-0059	2
Appr	SUDHIR VARMA	2010-02-23	Product family		D-SUB		Spec ref -
FCI		FEMALE CONNECTOR STD EURO		straight solder type for		C01-8646-0495	
catalog no		-		-		CUSTOMER	
						sheet 1 of 1	

1

2

3

4



Copyright FCI.