


A1 $\frac{\text{gray 1}}{(\text{interior-blue})}$
 B1 $\frac{\text{gray 2}}{(\text{interior-orange})}$
 A2 $\frac{\text{gray 3}}{(\text{interior-green})}$
 B2 $\frac{\text{gray 4}}{(\text{interior-brown})}$

9	FO break-out MPC cable, MM, 4-channel	33 54 111 300 0002	300 m
8	FO break-out MPC cable, MM, 4-channel	33 54 111 100 0002	100 m
7	FO break-out MPC cable, MM, 4-channel	33 54 111 060 0002	60 m
6	FO break-out MPC cable, MM, 4-channel	33 54 111 050 0002	50 m
5	FO break-out MPC cable, MM, 4-channel	33 54 111 040 0002	40 m
4	FO break-out MPC cable, MM, 4-channel	33 54 111 020 0002	20 m
3	FO break-out MPC cable, MM, 4-channel	33 54 111 010 0002	10 m
2	FO break-out MPC cable, MM, 4-channel	33 54 111 005 0002	5 m
1	FO break-out MPC cable, MM, 4-channel	33 54 111 001 0002	1 m
Cont No.	Type of cable	Part-No.	Dim. a

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances			
				Dat.	Name	Maßstab/Scale	Fiber optic cable assembly 1xHan 3A 2xLC DUPLEX, metal Multi Mode, 50 µm		
			Detail.	14.10.09	MS				
			Insp.	14.10.09	RA				
			Stand.						
DRS557A			HARTING Electronics GmbH & Co. KG				TB 33 54 111 xxx 0002		Blatt/ page /
Mod.	Dat.	Name	D-32339 ESPELKAMP				Sub. Sub		