






Family	inserts
Version	screw terminal connections
Series	CX
Product type	with female contacts
Model	female insert
Reference standard	EN 61984 (2001-11)
Contact type	silver plated
No. of poles	4 poles + 
Voltage (V)	690V
Current (A)	80A (A.C./D.C.)
Wire section	4mm ² - 16mm ²
Awg size	12 - 6
Quality mark	
IP degree of protection	IP20 degree of protection without enclosure; IP65, IP66, IP67, IP68 (EN 60529) and IP69K (DIN 40050 - 9) with enclosure
Fixing centre distance	size "77.27"
Impulse withstand voltage	8kV
Pollution degree	3
Barcode EAN13	8015747042314
Notes	CX 4/0 inserts: - characteristics according to EN 61984: (80A 690V 8kV 3)