


B



1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS:
 - A. SEE SHEET 2 FOR METHOD A.
 - B. SEE SHEET 3 FOR MODIFIED METHOD A, PAIR FLIPPED.
4. METHOD A CASSETTES COMPLY WITH ANSI/TIA-568-C.O. SEE ANSI/TIA-568-C.O FOR POLARITY DETAILS AND EXAMPLE OF A BASIC LINK.
5. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
6. CASSETTE WEIGHT: 3.53oz [100g]
7. DIMENSIONS IN BRACKETS ARE METRIC.



- SEE SHEETS 2 AND 3
FOR ARTWORK DETAILS

☐

SHOWN W/O DUSTCAPS

1

B

☐☐

A

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX LC CASSETTE - MODIFIED METHOD A, PAIR FLIPPED	
PART NUMBER	DESCRIPTION
FC2ZO-12-10AF	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-10AF	12 FIBER 50/125um OM4
FC2XO-12-10AF	12 FIBER 50/125um 10 GbE OM3 OPTIMIZED
FC2XN-12-10AF	12 FIBER 50/125um 10 GbE OM3
FC25N-12-10AF	12 FIBER 50/125um OM2
FC26N-12-10AF	12 FIBER 62.5/125um OM1
FC29N-12-10AF	12 FIBER 9/125um OS1
FC2SA-12-10AF	12 FIBER 50/125um OM4+, SIGNATURE CORE

B


B



MODIFIED METHOD A, PAIR FLIPPED - FIBER LAYOUT

A

A

							TITLE 12 FIBER DUPLEX LC CASSETTE MODIFIED METHOD A, PAIR FLIPPED CUSTOMER DRAWING							
							ITEM REVISION NAME 10F113AD/00			PANDUIT TM				
							DATASET FILE NAME 10F113AD_DC/00A							
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .03 (.8) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5 °  THIRD ANGLE PROJECTION			MATERIAL: SEE NOTES SHEET 1				
										DRAWING NUMBER: 10F113AD-DC				
R	10-10-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AD-DC	DRAWN BY SAT			DATE 10-01-12	CHK TMSE	SCALE NONE	SHT 3 OF 3	SIZE A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN								

2

1