

10112684 - X XX-YY Z LF

INDICATES THAT PRODUCT IS RoHS COMPATIBLE. SEE NOTE 3







PACKAGING :

- A = Tape and reel with Pick-up cap. See GS-14-1516 As available
- U = Tube without Pick-up cap. Only for contacts qty from 4 to 25. See GS-14-1551
- Blank = Bli box for contacts qty 2 and 3 See note 5

CONTACTS QTY : 02 to 25 = N

XX	01	02	03
DIM C POST LENGHT	3.2	2.0	4.0

PLATING : G= 0.76 μ Gold/GXT on mating area
 2-6 μ Pure Tin on solder area
 F= Gold flash on mating area
 2-6 μ pure Tin on solder area
 T= 2-6 μ pure Tin on mating area
 2-6 μ pure Tin on solder area
 All with 1.27 Ni underplating



- NOTES :
- 1- MATERIALS :
 BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0
 PIN : COPPER ALLOY
 - 2- 7N MIN PIN RETENTION IN EITHER DIRECTION
 - 3- RoHS COMPATIBLE PRODUCT SPECIFICATION :
 a- PLATING : LF means the product is Lead Free.
 2 μ MIN matte Tin over 1.27 μ Nickel underplating.
 b- MANUFACTURING PRODUCT SPECIFICATION :
 Housing will withstand exposure to 260 $^{\circ}$ C peak temperature for 30 secondes in a convection infra-red or vapor phase oven.
 - 4- ONE TIP OF BODY MIGHT BE WITHOUT INDENTS AS PER EXTREMITY OF MOLDED BODY.
 - 5- MINIMUM QUANTITY IN Bli BOX : 500

rev	ecn no	dr	date
A	F10-0082	LSA	10/07/30
B	F10-0227	APA	10/10/01
C	F10-0238	APA	10/10/21
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - ☒ ISO 1302	tolerance std ☒ ISO 406 ☒ ISO 1101	projection	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	L. SAILLARD	10/02/04	ANGULAR	0.X $\pm$	size A3	Scale 8:1
Eng	L. SAILLARD	10/02/04	LINEAR	0.XX $\pm$		
Chr	JM COMPAGNON	10/02/04	0° $\pm$	0.XXX $\pm$	ECN F10-0238	
Appr	/	/	Product family		Spec ref GS-12-652	
FCI			title SINGLE ROW ASSEMBLY			Rev. C
			MINITEK HEADER SMT R/A			
			catalog no			
			CUSTOMER			sheet 1 of 1