

DO NOT SCALE
DIMENSIONS IN

METRIC

3rd ANGLE PROJECTION

NOTES

- 1 MATERIAL: HOUSING: TERMOPLASTICO S/ FIBRA DE VIDRO V-0 COR: PRETO
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITHOUT GLASS FIBER V-0 COLOR: BLACK
CONTACT: PHOSPHOROUS BRONZE
- 2 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO HB COR: NATURAL
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER HB COLOR: NATURAL
CONTACT: PHOSPHOROUS BRONZE
- 3 0,38 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,38 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 4 0,76 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,76 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 5 1,27 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
1,27 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 6 ESTANHO SOBRE NIQUEL
TIN UNDER NICKEL
- 7 PONTO DE CONTATO E/ MEDIÇÃO DA CAMADA DE OURO
CONTACT POINT FOR GOLD PLATING MEASUREMENT
- 8 ACETA PINO QUADRADO 0,64 x 0,64 OU REDONDO Ø 0,64
ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND Ø 0,64
- 9 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO COR VERMELHO, V-2
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER COLOR RED; V-2
CONTACT: PHOSPHOROUS BRONZE

	3	10	L	2 - 880584	- 1
11 OBSOLETE	6	9			9
11 OBSOLETE	6				8
	5				- 7
11 OBSOLETE	4				6
	3	2			- 5
	6				- 4
11 OBSOLETE	5				- 3
	4				- 2
	3	1	K1	880584	- 1

OTHER TREATMENT			FINISH			MATERIAL			PART REV.	PART NUMBER								
CUSTOMER DWG for REFERENCE ONLY						TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,3 ANGLES ± 1°							INS. DIA. RANGE		WIRE RANGE		SCALE	
													—//—		—//—		—//—	
						DR.		TE Connectivity										
						CHK.		DESCRIPTION ..										
						DE.		AMP SHUNT CONNECTOR ASS'Y										
L4 REV. ECO 11-023509			HC	WLS	02DEC11													
L3 REVISED PER ECO-11-005139			RK	HMR	28MAR11													
153 REVISION RECORD			DR	CHK	DATE	APP	A3	DWG NO	C	880584		SHEET		1072				


C 880584

C

B

A

- 10 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO V-2 COR: VERDE
CONTATO: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-2 COLOR: GREEN
CONTACT: PHOSPHOROUS BRONZE
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



11 OBSOLETE	6			1	8
	5			1	7
	4			1	6
	3		2	1	5
	6			1	4
	5			1	3
11 OBSOLETE	4			1	2
	3		1	K1	1 - 880584 - 1

OTHER TREATMENT	FINISH	MATERIAL	PART REV.	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY		TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0.5 ANGLES $\pm 1^\circ$		
INS. DIA. RANGE		WIRE RANGE	SCALE	
TE Connectivity		DESCRIPTION AMP SHUNT CONNECTOR ASS'Y		
DWG NO A3		C 880584		SHEET 2 of 2
REVISION	RECORD	DR	CHK	DATE