





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIMENSIONS						WEIGHT lbs/100pcs (kg)/100pcs
	A (REF)	B (REF)	C	D	E (REF)	F	
BR-1.5-SN	1.50 [38]	3.15 [80]	0.32 [8] MINIMUM	0.206 [5.24] 0.203 [5.16]	2.00 [51]	.320 [8.1] .200 [5.1]	9.7 (4.4)
BR-2.0-SN	2.00 [51]	3.63 [92]	0.32 [8] MINIMUM	0.206 [5.24] 0.203 [5.16]	2.00 [51]	.320 [8.1] .200 [5.1]	10.9 (4.9)



ISOMETRIC VIEW

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. PART TO BE SECURED WITH USER SUPPLIED FASTENER.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03668DY_DC_GB3668DY/OOA

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

BR-_-SN
BRIDLE RING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]
(.XX) ±0.02 [0.5] ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY
ARHA

MAT'L: LOW CARBON
STEEL BRIGHT
ZINC
ELECTROPLATE

SCALE
NONE

DATE
09-15-09

DRAWING NO.
GB3668DY

CHK'D
KLW

DWG
A
SIZE

OOA	09/15/09	ARHA	KLW	INITIAL RELEASE	GB3668DY	OOA	KLW				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP			