



WESTCODE

SEMICONDUCTORS

 TECHNICAL
PUBLICATION

DP300

ISSUE 1

May, 1980

Stud-Base Silicon Rectifier Diodes Type PHN/PHR300

380 amperes average: up to 1500 volts V_{RRM}

RATINGS Maximum values at 180°C T_j unless stated otherwise

RATING	CONDITIONS	SYMBOL	
Average forward current	Half sine wave 100°C case temperature	$I_{F(AV)}$	380A
RMS current		$I_{F(RMS)}$	600A
DC forward current		I_F	600A
Peak one-cycle surge (non repetitive)	8.3ms duration $\left\{ \begin{array}{l} 60\% V_{RRM} \text{ re-applied} \\ V_R \leq 10 \text{ volts} \end{array} \right.$	$I_{FSM(1)}$ $I_{FSM(2)}$	5830A 6413A
Maximum permissible surge energy	8.3ms duration $\left\{ \begin{array}{l} 60\% V_{RRM} \text{ re-applied} \\ V_R \leq 10 \text{ volts} \end{array} \right.$ 3ms duration $V_R \leq 10 \text{ volts}$	$I^2 t (1)$ $I^2 t (2)$	147400A ² s 177510A ² s 135000A ² s
Case operating temperature		T_C	-30, +180°C
Storage temperature		T_{stg}	-40, +200°C

CHARACTERISTICS Maximum values at 180°C T_j unless stated otherwise

CHARACTERISTIC	CONDITIONS	SYMBOL	
Peak forward voltage drop	At 1180A, I_{FM}	V_{FM}	1.83V
Forward conduction threshold voltage		V_0	0.95V
Forward conduction slope resistance		r	0.75mΩ
Peak reverse current	At V_{RRM}	I_{RRM}	15mA
Thermal resistance junction to case for a diode with a maximum forward voltage drop characteristic	DC and 180° sine wave 120° rectangular wave	$R_{th(j-c)}$	0.13°C/W 0.14°C/W
Thermal resistance case to heatsink		$R_{th(c-hs)}$	0.04°C/W

VOLTAGE CODE →	02	04	06	08	10	12	14	15	
Repetitive voltage V_{RRM}	200	400	600	800	1000	1200	1400	1500	
Non-repetitive voltage V_{RSM}	300	500	700	900	1100	1300	1500	1600	

ORDERING INFORMATION (Please quote device code as explained below — 10 digits)

S	W	●	●	P	H	●	3	0	0
FIXED BASIC CODE	VOLTAGE CODE (see above)	FIXED OUTLINE CODE	STUD POLARITY N = cathode R = anode	FIXED TYPE CODE					

 Typical code SW06PHR300 = 600V_{RRM} diode with stud anode

In the interest of product improvement, Westcode reserves the right to change specifications at any time without notice.

