

Sales Outline Drawing

Revision

A


Specifications:

Oscillation Frequency (Hz)	2000 ~ 2500
Operating Voltage (Vdc)	3 ~ 10
Rated Voltage (Vdc)	6
Current Consumption Max. (mA)	40 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage
Coil Resistance (Ω)	60 ± 9
Operating Temperature ($^{\circ}\text{C}$)	-30 ~ +70
Storage Temperature ($^{\circ}\text{C}$)	-40 ~ +85
Housing	NORYL
Weight (Grams)	7.0
Options	For other options contact factory


PS: V_{p-p} = 1/2duty, square wave

RoHS Compliant

Dimensions: (units: mm)



Recommended Driving Circuit:



The base current I_b should be high enough so that it saturates the collector current of the transistor with the CB load.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-1820PL-06AQ](#)