






CONTACT: BERYLLIUM COPPER
PLATED GOLD 30u" MIN. OVER NICKEL 50u" MIN.
(73366-6190/6191 PLATING SEE TABLE)

BODY: BRASS
PLATED SEE TABLE



73366-6192	.280±.006	7.10±0.15	.062±.006	1.58±0.15	.073±.006	1.86±0.15	GOLD 1u" MIN.	CONTACT GOLD 1u" MIN. ; TAPE & REEL
73366-6191	.280±.006	7.10±0.15	.062±.006	1.58±0.15	.073±.006	1.86±0.15	GOLD 1u" MIN.	73366-0061 TAPE & REEL
73366-6190	.579±.006	14.70±0.30	.062±.006	1.58±0.15	.071 REF	1.81 REF	GOLD 1u" MIN.	CONTACT GOLD 10u" MIN. ; TRAY
73366-0069	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	GOLD 1u" MIN.	1 PC 73366-0061 PER BAG
73366-0068	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	NICKEL 70u" MIN.	73366-0060 SMALL TRAY
73366-0067	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	NICKEL 70u" MIN.	1 PC 73366-0060 PER BAG
73366-0066	.236±.006	5.99±0.15	.019±.006	0.50±0.15	.031±.006	0.80±0.15	GOLD 1u" MIN.	73366-0065 TAPE & REEL
73366-0065	.236±.006	5.99±0.15	.019±.006	0.50±0.15	.031±.006	0.80±0.15	GOLD 1u" MIN.	TRAY
73366-0064	.236±.006	5.99±0.15	.019±.006	0.50±0.15	.031±.006	0.80±0.15	NICKEL 70u" MIN.	73366-0063 TAPE & REEL
73366-0063	.236±.006	5.99±0.15	.019±.006	0.50±0.15	.031±.006	0.80±0.15	NICKEL 70u" MIN.	TRAY
73366-0062	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	NICKEL 70u" MIN.	73366-0060 TAPE & REEL
73366-0061	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	GOLD 1u" MIN.	TRAY
73366-0060	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	NICKEL 70u" MIN.	TRAY
PART NO.	IN	MM	IN	MM	IN	MM	PLATING	CONTACT PLATING & PACKAGE
DIM (X)	DIM A		DIM B		DIM C		BODY	




PS-73598-0132	ELECTRO /MECH PERFORM.
SPECIFICATION	DESCRIPTION


DOCUMENT STATUS	P1	RELEASE DATE	2022/09/13	09:16:28
-----------------	----	--------------	------------	----------





FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
F/A = 0 F/C = 0 F/P = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: EWR # 15425-A ADDED TRAY PACKING DRAWING				molex MCX JACK VERT PCB TH 50 OHMS MCX-J/PCB EWR-3263									
		MM/INCH		NTS															
		GENERAL TOLERANCES (UNLESS SPECIFIED)								EC NO: 720553 DRWN: JSU18 2022/09/07 CHK'D: YCHENG 2022/09/13 APPR: YCHENG 2022/09/13 INITIAL REVISION: DRWN: JTSAO 2006/04/20 APPR: MISEN 2001/03/01				PRODUCT CUSTOMER DRAWING					
		ANGULAR TOL ± 2.0°																	
		4 PLACES		±		DOCUMENT NUMBER												DOC TYPE	
		3 PLACES		±		SD-73366-006								PSD		001		C3	
		2 PLACES		±															
1 PLACE		±																	
0 PLACES		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		73366		SEE TABLE		GENERAL MARKET		1 OF 5					

1. TAPE AND REEL PACKAGE
2. 10 PITCHES CUMULATIVE TOLERANCE $\pm 0.20(.008)$

A

FORMAT: master-ib-prod-C	12	11	10
REVISION: 21			
DATE: 2021/05/01			





FORMAT: master-ib-prod-C	12	11	10
REVISION: J1			

