

- Exact colour, high quality LED lighting.
- VxRGB Vivid Vision brings excellent colour appearances and a much wider and richer spectrum than conventional LED light source.
- VxRGB ensures that colours appear as they should do and illuminates objects in finer detail.
- Dimmable
- Perfect lighting for art gallery, fashion stores, restaurants and other application areas where vivid and accurate lighting is required.

VxRGB
LED LIGHTING



Order Code 52224

General Data

Lamp Socket GU5.3

Design Lens

Geometric Data

Length (mm) 50

Diameter (mm) 50

Weight (g) 50

Electric Data

Wattage (W) 6.5

Voltage (V) 12 V AC/DC

Power Factor

Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 180

CRI ≥ 85

CCT (K) 2900

Luminous Intensity (cd) 300

Beam Angle (°) 36

Lifetime (hrs) 25,000

Switching cycle 18,000

Wattage Equivalent (W) Up to 20W





Order Code

52224

Product Description

Verbatim VxRGB V-series LED MR16 GU5.3 6.5W 2900K WW 180LM 36DEG DIM

Technical Packaging Details

Barcode	023942522249
EAN 128	(02)00023942522249(37)40(91)162
EAN 14	50023942522244
Pack Dimensions (HxWxL)	62 mm x 50 mm x 50 mm
Pack Weight	77 g
MOQ	10
Carton Dimensions (HxWxL)	330 mm x 300 mm x 150 mm
Cartons/Pallet	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52224

