




Protection class to EN 60 529:

IP 66 / 67

Flame protection:

Glow wire test 750° C acc. to EN 60695-2-11

Temperatures during installation:

-5°C to 60°C

Temperature range of material:

-30°C to 100°C, intermittent up to approx. 120°C

Voltage:

690 V

Material:

Polypropylene, reinforced glass fibre; sealing: thermoplastic elastomere

Terminals/poles:

6 mm²

Fixing:

4 internal openings outside of the sealing area

Equipment:

Elastic self-sealing membranes for cable entry without mechanical devices: 7 inlets at the side and 3 inlets in the base

- 7 integrated M 25 threads, no locknuts necessary

- 4 captive quick-release lid screws

- Colour RAL 7035 light grey

- .../S = black

- .../W = white

Accessories:

- DIN RAIL KIT 607: Rail TS 35 + Fixing material, WISKA-No. 10060361

- EC 607 Earthing plate: WISKA No. 10101474

Type	WISKA-No.		 mm		L x B x H external/external mm
COMBI 607/5	10060532	3/27	3 - 17		110 x 110 x 66
COMBI 607/5/S	10060538	3/27	3 - 17		110 x 110 x 66
COMBI 607/5/W	10060534	3/27	3 - 17		110 x 110 x 66
DIN RAIL KIT 607	10060361	1			-