

NorComp

Quick Reference Guide to D-Sub Backshells

Series	Material			Cable Entry							Hardware				Standard	High Density
	70db Die Cast	60db Metalized	Plastic	180°	90°	60°	45°	40°	35°	3-way	Standard		Other Hardware types available	Strain Relief type	Connector Size	Connector Size
											4-40 std. screws	4-40 thumb- screws				
950		x	x			x					x		M3	Mechanical	9,15,25,37	15,26,44,62
951		x	x			x						x	M3	Mechanical	9,15,25,37	15,26,44,62
952	x			x								x	M2.5-M3-M2.6	Mechanical	9,15,25,37	15,26,44,62
953	x								x			x	M2.5-M3-M2.6	Mechanical	9,15,25,37	15,26,44,62
954	x						x						Slide Lock	Compression	9,15,25,37	15,26,44,62
955	x	x	x							x			Quick Lock	Mechanical	9,15,25,37	15,26,44,62
956		x	x	x							x			Compression	9, 15, 25	15,26,44
957		x	x	x							x			N/A	9,15,25, 9-to-25	15,26,44, 15-to-44
958			x	x							Female Screw Locks			N/A	9, 15, 25	15,26,44
970	x	x	x	x								x	x	Compression	9,15,25,37	15,26,44,62
971	x	x	x				x					x	x	Compression	9,15,25,37	15,26,44,62
972			x	x								x		Mechanical	9,15,25,37	15,26,44,62
973		x	x	x								x		Mechanical	9,15,25,37	15,26,44,62
974		x	x			x						x		Mechanical	9,15,25,37	15,26,44,62
975		x	x							x		x		Mechanical	9,15,25,37	15,26,44,62
976		x	x	x							x			Compression	9,15,25,37	N/A
977		x	x	x							x	x		Mechanical	9,15,25,37,50	15,26,44,62,78
978		x	x	x							x	x		Compression	9,15,25,37,50	15,26,44,62,78
979	x	x	x	x							x	x	x	Compression	9,15,25,37,50	15,26,44,62,78
981	x				x						x	x		Compression	9,15,25	15,26,44
982		x	x	x			x				x			Mechanical	9,15,25,37,50	15,26,44,62,78
983		x	x	x							x	x		Mechanical	9,15,25,37,50	15,26,44,62,78
993		x	x		x							x		Mechanical	9,25	15,44
994	x			x							x			Mechanical	9,15,25	15,26,44

New

NorComp Backshell Part Number Key:

Series Positions Material RoHS Color Put-up

970 - 025 - 040 R 01 1

Example: 970-025-040R011

9 Pos. Standard & 15 Pos. High Density use 9 Pos. Backshells
 15 Pos. Standard & 26 Pos. High Density use 15 Pos. Backshells
 25 Pos. Standard & 44 Pos. High Density use 25 Pos. Backshells
 37 Pos. Standard & 62 Pos. High Density use 37 Pos. Backshells
 50 Pos. Standard & 78 Pos. High Density use 50 Pos. Backshells