

You are here: [Products](#) » [Connectors f.con](#) » [D-Sub connectors](#) » [D-Sub standard connectors](#) » [DS WR 3 ... / DS WR 4 ...](#) [DB WR 3 ... / DB WR 4](#) » [DS WR 4](#)



► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

► PCB connectors

► IDC-connectors

▼ D-Sub connectors

■ [D-Sub standard connectors](#)

■ D-Sub connectors High Density

■ D-Sub filter connector

■ D-Sub connector for flat ribbon cable

■ D-Sub mixed layout connectors

■ D-Sub in SMD-mounting

■ D-Sub connector in pressfit technology

■ D-Sub hoods

■ D-Sub accessories

■ Brackets for PC

► Optoelectronics

D-Sub standard connectors

DS WR 3 ... / DS WR 4 ...
DB WR 3 ... / DB WR 4

DS WR 4 9

plastic angle with earthing plate, snap-on clip and threaded rivet UNC 4-40

Data sheet

add to request



Features

Technical Drawing

Variants

Service

contact material

Cu-alloy

surface contact /

hard gold plated over nickel

contact sleeve

quality class / cyces of operation quality class 2 = 200 cycles of operation

volume resistance

≤10 mΩ before strain, ΔR 10 mΩ after strain according to DIN 41652. part 2 (MIL-C-24308)

air gap and creep distance

cont.-contact <1mm

contact-earth <1mm

nominal current

5A (20°C)

nominal voltage

125 V AC

test voltage

1000 V

insulating body material

PBT, GF

temperature range

-55°C... +125°C

casing frame

steel, tin plated

class of inflammability

UL 94 V-0

fixing part

plastic angle with earthing plate, threaded rivet UNC 4-40, snap-on clip

insulation resistance

≥5 GΩ