

Features



- ## Performance Specifications

Materials and Finish

Body: PBT Thermoplastic, UL94V-2 Rated, Black Color

Contacts: Phosphor Bronze, Tin/Lead Plated

Mechanical Characteristics

Insertion Force

11.0kg Max.

Extraction Force

1.1kg - 7.0kg

Electrical Characteristics

Current Rating

3.0A 100V AC

Contact Resistance

20 Megohms Max.

Insulation Resistance

100 Megohms Min. at 500V DC

Dielectric Withstanding Voltage

800V AC for 1 Minute

Operating Temperature

-25°C to +85°C

Ordering Information


Part Number	Description
K-SCART-021	Single 21 Position, Right Angle
K-SCART-028A	21 Position Over 21 Position, Right Angle
K-SCART-022	Single 21 Position, Right Angle, Slim
K-SCART-024	Single 21 Position, Vertical

K-SCART Series


K-SCART Series Dimensions

Dimensions in mm

K-SCART-021






K-SCART-028A



K-SCART Series Dimensions

Dimensions in mm

K-SCART-022






SCART CONNECTORS

K-SCART Series

K-SCART Series Dimensions

Dimensions in mm

K-SCART-024



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K-SCART-029A](#) [K-SCART-024](#) [K-SCART-021](#) [K-SCART-022](#) [K-SCART-028A](#)