

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100038](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Pro-Yellow 400W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 0.91m (3.0') for Canada

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E174253
General	
Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Pro-Yellow
Type	Wide Area Lamps
UPC	78678887565
Physical	
Cord Length - Primary	0.91m (3.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Steel
Height	463.55mm (18.250")
Length	N/A
Material - Guard	#10 Gauge Zinc-plated Steel
Mounting Style	Hook
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Metal Halide - Probe Start
Cord Type - Primary	16/3 SJTOW
Lamp Type	BT37/ED-37 Type O
Lamp Wattage - Maximum	400W
Lumens	26000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	8575-MH



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130110](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION