

Search within category

GO

BUY NOW

DESIGN / INSTALL

HB1A1M2BN12E1

The 30A, 120V horizontal power strip in black has 12 NEMA 5-20R receptacles. It features two 20A single-pole magnetic breaker on-off switches and integral switch guard, a red LED current monitor, and a 10' (3m) power cord with a NEMA L5-30P twist-lock plug. It is UL and c-UL listed and measures 1.7H x 17.0W x 6.5D (43mm x 432mm x 165mm). It is sold individually.

This part number has been obsoleted with no replacement. [Click here](#) to contact customer service for further assistance.

Specs

Packaging Details

Documents

OM Obsolete Code	OBSOLETE
Rack PDU Type	Basic Rack PDU with Local Meter
Monitoring	Local Meter
Remote Outlet Switching	No
Mount Orientation	Horizontal
Current Rating (Amps)	30A
Input Voltage	120V - Single Phase
Plug Type	NEMA L5-30P
Output Voltage	120V
Receptacle Type	NEMA 5-20R Duplex
Total Number of Outlets	12
Depth (In.)	6.50
Depth (mm)	165.1
Height (In.)	1.72
Height (mm)	43.7
Width (In.)	17.10
Width (mm)	434.3
Tool-Less Button Spacing (In.)	NA
Tool-Less Button Spacing (mm)	NA
No. of Rack Spaces	1
Surge Suppression	No
Amps	30A
Cable Length	3
Length (In.)	22.50
UL Recognized	Yes
Voltage	120V
RoHS Compliancy Status	Compliant
Min. Order Qty.	1