

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936000028
Status: Active
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Metal Cable Gland - 5 Bar, for 14.00-21.00mm Cable, M32x1.5 Thread



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Industrial Connectors / Enclosures
Series 93600
Cable Gland Type IP68 - 5 Bar
IP Rating IP68
Overview GWconnect Heavy Duty Connectors (HDC)
Product Category Cable Glands
Product Name GWconnect
UPC 887191822600

Physical
Cable Diameter 14.00-21.00mm
Flammability UL 94V-0
Material - Cable Gland Brass
Material - Plating Nickel
Net Weight 117.000/g
Packaging Type Bag
Panel Cutout Diameter 32.50mm
Temperature Range - Operating -40°C to +125°C
Thread Size M32x1.5
Thread Type (M) Metric
Waterproof / Dustproof Yes
Waterproof / Dustproof Type IP68

Material Info
Engineering Number 7000.6833.0

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93600 Series](#)

Use With
Industrial connector hoods and housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION