

HC-B 10-TFL-72/O1M25S

Order No.: 1604763



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1604763>

HEAVYCON sleeve housing B10, for single locking latch, height 72 mm, with support 1x M25, lateral conductor exit

Commercial data

GTIN (EAN)	4 017918 882556
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 482 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Design	B10
Height	72 mm
Width	43 mm
Length	73 mm

Housing type	Sleeve housings
Locking type	for single locking latch
Cable exit	Lateral
Type of the screw connection	1x M25
Wrench size, union nut	25 mm
External cable diameter	9 mm ... 18 mm
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;