


12 VDC Socket and Harness

161-65B2-E

KOBI CONN

12 VDC Socket and Harness



Dimensions: mm (In.)

SPECIFICATIONS

Rating:	12 VDC 10A max.
Contact resistance:	50mΩ max.
Insulation resistance:	100MΩ min. @ 500VDC
Dielectric Strength:	1500VAC for 1 minute
Operation Torque:	-30°C to 70°C

MATERIALS

Fuse:	10A ø6.4*30
Wire:	18AWG
Terminals:	Copper alloy, nickel plated
Dust Cover:	PVC
Housing:	Nylon-66

Date Last Revised: 9-12-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-301068

161-65B2-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-65B2-E](#)