






CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE B (WITH INTERNAL SPRING)



TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-... A/O 929937-... AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)

CONNETTORE OR CENTER LINE)			3	\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)	
			2	NATURALE (NATURAL)	GOMMA SILICONE (SILICONE RUBBER)	GUARNIZIONE (SEALING)	
			1	\\\\\\\\\\\\\\	PA 6.6	BLOCCHETTO (HOUSING)	
GRIGIO (GREY)	282766-2	E	N°	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	
NERO (BLACK)	282766-1		REV. ASSY				
COLORE (COLOR)	NUMERO (PART. N°)		CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
			THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19				
			© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING				
			TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0 (RED. INS. CABLE)	RANGO FILO (WIRE RANGE) 0.5-2.5 mm ²	
			± 0.3		SCALA (SCALE) ---		
			ANGOLI (ANGLES) ± 2°		 TE Connectivity		
E	ECR-14-003472	MP	24MAR 2014	DIS. 22 AUG 95 (DR.) A. BAJ		DESCRIZIONE (DESCRIPTION) 5 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK	
C	AGGIORNATO E IN PRODUZIONE ET00-0125-00	M. P.		CONT. 22 AUG 95 (CHK) C. TARTARI			
B	AGGIORNATO E IN PRODUZIONE EC ET00-0075-96	A. B.	12-9 1996				
A	PRIMA EMISSIONE CON ECN ET00-0217-95	A. B.	15-9 1995			LOC. SIZE NUMERO (DWG NO)	
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. - (APP.)				
			I	A3	C-282766	REV. E	FOGLIO (SHEET) 1 DI 2 (OF)

DISTRIBUZIONE
(PRINT DIST.)

ASSE
CONNETTORE
(CONN. CENTER
LINE)

ASSE CAVITA'
(CAVITY CENTER LINE)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN
(DIMENSIONS IN) mm

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

DETT. LINGUETTA TAB-SCALA 5:1-
(TAB DETAIL)

FORMA ALTERN. PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)

VISTA DA "B"
(VIEW FROM "B")

- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO
(DRAFT PERMITTED TO FACILITATE REMOVAL OF PART
FROM THE MOULD)
- 2 MATERIALE LINGUETTE: LEGA DI RAME
STAGNATA, ES. OTTONE STAGNATO.
(TAB CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
E.G. BRASS TIN PLATED)
- 3 MATERIALE BLOCCHETTO: TERMOPLASTICO
CARICATO FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC, GLASS FIBER
FILLED)

FINITURA / COLORE
(FINISH / COLOUR)

MATERIALE
(MATERIAL)

NUMERO
(PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

± 0.3

ANGOLI
(ANGLES)

± 2°

DIS.
(DR.)

CONT.
(CHK)

DESCRIZIONE (DESCRIPTION)

5 POS. SPLASH PROOF CONN. ASS'Y
with SECONDARY LOCK

LOC. SIZE NUMERO
(DWG NO.)

REV. FOGLIO
(SHEET)

I A3 C-282766

2 OF 2

REV. REVISIONI
(REVISION RECORD)

DIS. DATA
(DR) (DATE)

DISTRIBUZIONE
(PRINT DIST.)