

# Plug 'n' Play compact axial fans

Complete with mountings and connector



- DC fans
- Plastic housing
- Ideal for PC cooling
- Molex connector fitted
- Connection via lead 313mm (+/- 10mm)
- Threaded brass inserts fitted on both sides
- Blowing over struts
- Protection IP20

|              | Airflow | Airflow | Voltage | Voltage Range | Noise | Sound Power | Bearings | Power | Speed | Temp range | Length | Width | Depth | Insert thread size | Connector        |
|--------------|---------|---------|---------|---------------|-------|-------------|----------|-------|-------|------------|--------|-------|-------|--------------------|------------------|
| Part Number  | m³/h    | CFM     | VDC     | VDC           | dB(A) | Bel         |          | W     | RPM   | °C         | mm     | mm    | mm    |                    |                  |
| 624N-RS0     | 40      | 23.5    | 24      | 12...28       | 35    | 4.7         | Ball     | 2.2   | 6100  | -20...+70  | 60     | 60    | 25    | M3                 | Molex 22-01-2025 |
| 624HH-RS0    | 56      | 33      | 24      | 18...28       | 43    | 5.6         | Ball     | 3.6   | 8200  | -20...+70  | 60     | 60    | 25    | M3                 | Molex 22-01-2025 |
| 614NGML-RS0  | 25      | 14.7    | 24      | 18...28       | 19    | 3.9         | Sleeve   | 1.2   | 3000  | -20...+70  | 60     | 60    | 25    | M3                 | Molex 22-01-2025 |
| 614NGH-RS0   | 46      | 27.1    | 24      | 18...28       | 38    | 5.5         | Sleeve   | 2.6   | 5600  | -20...+70  | 60     | 60    | 25    | M3                 | Molex 22-01-2025 |
| 714F-RS0     | 44      | 25.9    | 24      | 18...28       | 38    | 5.3         | Sleeve   | 1.5   | 5300  | -20...+70  | 70     | 70    | 15    | M3                 | Molex 22-01-2025 |
| 8412NGME-RS0 | 58      | 34.1    | 12      | 8...15        | 26    | 4.3         | Sleeve   | 1.4   | 2600  | -20...+75  | 80     | 80    | 25    | M3                 | Molex 22-01-2025 |
| 8412NG-RS0   | 69      | 40.6    | 12      | 8...15        | 32    | 4.7         | Sleeve   | 2.0   | 3100  | -20...+70  | 80     | 80    | 25    | M3                 | Molex 22-01-2025 |
| 8412NH-RS0   | 79      | 46.5    | 12      | 8...13.2      | 37    | 5.0         | Ball     | 2.2   | 3600  | -20...+70  | 80     | 80    | 25    | M3                 | Molex 22-01-2025 |
| 8414NGL-RS0  | 33      | 19.4    | 24      | 18...28       | 12    | 3.5         | Sleeve   | 0.7   | 1500  | -20...+70  | 80     | 80    | 25    | M3                 | Molex 22-01-2025 |
| 8214JN-RS0   | 132     | 77.7    | 24      | 18...26.4     | 55    | 6.6         | Ball     | 10.0  | 8400  | -20...+70  | 80     | 80    | 38    | M3                 | Molex 22-01-2025 |
| 3412NGH-RS0  | 94      | 55.3    | 12      | 8...15        | 36    | 5.0         | Sleeve   | 2.5   | 3000  | -20...+70  | 92     | 92    | 25    | M3                 | Molex 22-01-2025 |
| 3314-RS0     | 80      | 47.1    | 24      | 12...28       | 37    | 5.2         | Ball     | 2.6   | 3000  | -20...+75  | 92     | 92    | 32    | M3                 | Molex 22-01-2025 |
| 4412FM-RS0   | 140     | 82.4    | 12      | 7...12.6      | 38    | 4.8         | Ball     | 3.2   | 2400  | -20...+75  | 119    | 119   | 25    | M3                 | Molex 22-01-2025 |
| 4414FM-RS0   | 140     | 82.4    | 24      | 12...28       | 38    | 4.8         | Ball     | 3.2   | 2400  | -20...+75  | 119    | 119   | 25    | M3                 | Molex 22-01-2025 |
| 4414F-RS0    | 170     | 100.1   | 24      | 12...28       | 43    | 5.3         | Ball     | 5.0   | 2900  | -20...+60  | 119    | 119   | 25    | M3                 | Molex 22-01-2025 |

## Fixing Centres

| Frame Size | Dimension A (mm) |
|------------|------------------|
| 60         | 50               |
| 70         | 61.5             |
| 80         | 71.5             |
| 92         | 82.5             |
| 119        | 104.8            |

