

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F


ZONE

LTR

DESCRIPTION

DATE

APPD



METRIC						3.18-4.19 DIA [.125-.165]	0.3 -0.8mm [22-18] AWG	63612-1
						INSULATION RANGE	WIRE RANGE	PART NO
F OR 0	5.59 [.220]	F	2.54 [.100]	1.57 [062]	0.8mm [18]	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.25 [.010] 3 PLC DEC ± - ANGLES ± - MATERIAL BRASS FINISH 0.002032 [.000080] MIN TIN PL PER MIL-T-10727 DR 1/10/91 P FORTNEY CHK 1/14/91 MS FEHER APPD 1/14/91 G YETTER APPD 1/14/91 R WEAVILL PRODUCT SPEC - APPLICATION SPEC - WEIGHT - AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME RING,AMPLIVAR™ SIZE B CAGE CODE 00779 DRAWING NO 63612 SCALE 4:1 SHEET 1 OF 1		
TYPE	WIDTH	TYPE	WIDTH	±0.051 [±.002] HEIGHT	WIRE			
INSUL BARREL CRIMP		WIRE BARREL CRIMP						