


D

C

B

A



LEGEND  
MADE IN SWEDEN  
PATENT PENDING

BLADE ADJUSTMENT  
HEX SCREWS (3)  
REPLACEABLE BLADE CASSETTE  
INSIDE TOOL.

1. 2mm HEX KEY 603988-1, SUPPLIED WITH EACH KIT.
  2. FOUR "V" BLOCKS & ADJUSTMENT GAUGE, SUPPLIED WITH EACH KIT.
  3. TOOL KIT PACKED IN VINYL POUCH OR BOX WITH PART NUMBER AND MADE IN SWEDEN ON LABELS
  4. SHIPPING WEIGHT .19 Lb.
- △ SAME AS 603995-1 EXCEPT, 10 PER PACKAGE

| TOOL KIT NO. | CASSETTE |
|--------------|----------|
| 603995-1     | 603996-1 |
| 603995-2     | 603996-2 |
| 603995-3     | 603996-3 |
|              |          |
| 603995-5     | 603996-4 |
| 603995-6     | 603996-5 |

| 2 STEP STYLE FOR SINGLE CRIMP BNC△         | 603995-9 |
|--------------------------------------------|----------|
| 3 STEP STYLE FOR DUAL CRIMP COMMERCIAL BNC | 603995-6 |
| 3 STEP STYLE FOR DUAL CRIMP BNC            | 603995-5 |
| 2 STEP STYLE FOR ECONOMY UHF               | 603995-3 |
| 2 STEP STYLE FOR COMMERCIAL BNC            | 603995-2 |
| 2 STEP STYLE FOR SINGLE CRIMP BNC          | 603995-1 |
| DESCRIPTION                                | PART NO  |

| "V" BLOCK |        | CABLE                 |             |
|-----------|--------|-----------------------|-------------|
| PART NO.  | COLOR  | DIA. RANGE            | RG #        |
| 603997-1  | RED    | 3.05-5.08 [.120-.200] | 195         |
| 603997-2  | BLUE   | 5.08-6.35 [.200-.250] | 58, 59, 62  |
| 603997-3  | YELLOW | 6.35-7.62 [.250-.300] | BELDEN 8281 |
| 603997-4  | WHITE  | 2.54-3.05 [.100-.120] | 174, 188    |

|                                                                                       |  |                               |                                     |                        |                    |
|---------------------------------------------------------------------------------------|--|-------------------------------|-------------------------------------|------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>J.L.GROFT<br>6-21-95   | TE Connectivity                     |                        |                    |
|                                                                                       |  | CHK<br>R.J.KOBLER<br>6-21-95  |                                     |                        |                    |
| DIMENSIONS:<br>MM [INCHES]                                                            |  | APVD<br>R.J.KOBLER<br>6-21-95 | NAME<br>COAXIAL CABLE STRIPPER<br>- |                        |                    |
|                                                                                       |  | PRODUCT SPEC<br>-             |                                     |                        |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                |  | APPLICATION SPEC<br>-         | SIZE<br>A3                          |                        |                    |
| 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± 0.38 [.015]<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |  | WEIGHT<br>-                   |                                     |                        |                    |
| MATERIAL<br>-                                                                         |  | FINISH<br>-                   | CAGE CODE<br>00779                  | DRAWING NO<br>C-603995 | RESTRICTED TO<br>- |
| CUSTOMER DRAWING                                                                      |  |                               | SCALE<br>1:1                        | SHEET<br>1 of 1        | REV<br>P           |