


Model BNC-C BNC Male To Male Cable Assembly



Part No.	Cable Type	Capacitance PF/ft.	Nominal Impedance	Cable Color	Cable O. D.
BNC-C-XX	RG58C/U	30.8	50 Ohms	Black	0.195"

MATERIALS:

BNC Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Brass

Dielectric: PTFE

RATINGS:

Operating Voltage: Shield-Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +80°C (+176°F) Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model BNC-C-XX

XX = Cable Length in inches, length tolerance: ± 0.5 "

Standard Lengths: 18", 24", 36", 48", 60", 72", 96", & 600".

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA