



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Waber-by-Tripp Lite 5-outlet Power Strip with 15-ft. Cord

MODEL NUMBER: **602-15**



Description

The Waber-by-Tripp Lite 602-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center spacing, 15-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, 15-amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 5 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center outlet spacing
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15-amp power handling capacity with circuit breaker
- 15-foot AC line cord

Specifications

OVERVIEW

Intended Application

Home/Office; Industrial/Factory Floor

Highlights

- 5 outlets
- 15-ft. cord
- 8.6-in. overall length
- No switch
- All-metal housing

Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power to protected equipment.

Package Includes

- 602-15 Power Strip
- Warranty information
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	5 NEMA 5-15R
Outlet spacing	1.188 in.
Outlet orientation	Single row of 5
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.572
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No switch
PHYSICAL	
Unit Dimensions (HWD/in)	7.38 x 2.5 x 1.5
Unit Dimensions (HWD/cm)	18.7 x 6.35 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
AC line cord color	Black
Style	Strip
Outlets center to center measurement	30mm
Keyhole slot center to center measurement	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[602-15](#)