

DISSTON HOL



5000 SERIES
PRO-Select
Bi-Metal
4/6 Variable
Tooth Design
- Fast cut



Carbide Tipped
PRO-Select
Deep Cut

4/6 VARIABLE TOOTH DESIGN - 'FAST CUT'


- CUTS UP TO 40% FASTER THAN CONVENTIONAL BI-METAL HOLESAWS
- LOWER FEED PRESSURE - IDEAL FOR HIGHER RPM OF TODAY'S PORTABLE DRILLS
- CLEARS CUT FASTER, STAYING SHARPER LONGER - SAVES TIME AND MONEY
- THICKER STEEL BACK - PREVENTS SCREW STRIPPAGE
- CUTS STAINLESS STEEL, TOOL STEEL, CAST IRON, ALUMINIUM, BRASS, WOOD AND PLASTIC
- USED IN ELECTRICAL, BUILDING, PLUMBING AND AUTOMOTIVE TRADES AND INDUSTRIAL PRODUCTION AND MAINTENANCE
- 1 1/8" DEPTH OF CUT - 51 SIZES - BOXED OR CARDED FOR DISPLAY
- ARBORS INTERCHANGEABLE WITH ALL MAJOR HOLESAW BRANDS

CARBIDE TIPPED DEEP CUT HOLESAWS

- LASTS UP TO FIVE TIMES LONGER THAN CONVENTIONAL HOLESAWS
- CUTS LAMINATED CONTIBOARD, GLASS FIBRE, PLYWOOD, INSULATION BOARD, INSULATION BLOCKS AND CERAMIC TILES
- 1 1/8" DEPTH OF CUT - 14 SIZES - 3 TPI
- ARBORS INTERCHANGEABLE WITH ALL MAJOR HOLESAW BRANDS

ARBORS (MANDRELS)

- OUR ARBORS ARE INTERCHANGEABLE WITH ALL NATIONAL BRANDS
- EIGHT MODELS COMPLETE WITH 6.5 (1/4") SPLIT POINT HSS PILOT DRILL WHICH ADJUSTS TO 3 LENGTHS, (5885 AND 5889 MODELS HAVE A SHORTER NON-ADJUSTABLE DRILL)
- QUICK CHANGE MODELS 5204 5887 PERMIT INSTANT CHANGE OF HOLESAWS WITHOUT REMOVING ARBOR FROM CHUCK. DRIVE PINS ALLOW MORE TORQUE = FASTER CUTTING SPEEDS = LONGER SAW LIFE
- ARBORS ARE FULLY HEAT TREATED FOR MAXIMUM WEAR RESISTANCE. THEIR SHANKS FIT ANY TWO OR THREE JAWED DRILL CHUCK



SPECIFICATION - ARBORS

DISSTON CODE NO.	STARRETT	SANDVIK	FITS HOLESAW SIZES in (mm)	CHUCK SIZE in (mm)	SHANK SIZE in (mm)
D5884	A4	ARBR-630	9/16 (14) - 13/16 (30)	1/4 (6.5)	1/4 (6.5) Round
D5889	-	-	9/16 (14) - 13/16 (30)	1/4 (6.5) 3/8 (9.5) 1/2 (13)	1/4 (6.5) Universal
D5885	-	-	1 1/4 (32) - 2 (51)	1/4 (6.5) 3/8 (9.5) 1/2 (13)	1/4 (6.5) Universal
D5886	A11	ARBR-1130	9/16 (14) - 13/16 (30)	1/2 (13)	7/16 (11) Hex
D5203	A1	ARBR-930	9/16 (14) - 13/16 (30)	3/8 (9.5)	3/8 (9.5) Hex
D5201	A6	-	1 1/4 (32) - 2 1/2 (64)	1/2 (13)	7/16 (11) Hex
D5204	A2	ARBR-11152	1 1/4 (32) - 6 (152)	1/2 (13)	7/16 (11) Hex Quick Change
D5887	A3	ARBR-16152	1 1/4 (32) - 6 (152)	3/4 (19)	3/4 (16) Hex Quick Change

ESAWS AND ARBORS


4/6 VARIABLE TOOTH

HOLES AW KITS


ALL COMPLETE IN HEAVY DUTY POLYETHYLENE CASES




D9595 HANDIMAN KIT
Contains five popular bi-metal HSS holesaws, diameters $\frac{7}{8}$ ", 1", $1\frac{1}{4}$ ", $1\frac{3}{4}$ ", $1\frac{1}{2}$ " (22mm, 25mm, 29mm, 32mm, 38mm) D5884 arbor + adaptor D5511.




D9592 PLUMBERS KIT
Contains holesaw sizes $\frac{3}{4}$ ", $\frac{7}{8}$ ", $1\frac{1}{8}$ ", $1\frac{1}{2}$ ", $1\frac{3}{4}$ ", $2\frac{1}{4}$ " (19mm, 22mm, 29mm, 38mm, 44mm, 57mm) arbors D5884, D5204 + D5511 arbor adaptor



D9596 ELECTRICIANS & PLUMBERS TRADESMANS KIT
Contains holesaw sizes $\frac{3}{4}$ ", $\frac{7}{8}$ ", $1\frac{1}{8}$ ", $1\frac{3}{8}$ ", $1\frac{1}{2}$ ", $1\frac{3}{4}$ ", 2", $2\frac{1}{4}$ ", $2\frac{1}{2}$ " (19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm) arbors D5884, D5204 + D5511, adaptor, $\frac{1}{4}$ " pilot drill D8535



D9593 ELECTRICIANS KIT
Contains holesaw sizes $\frac{5}{8}$ ", $\frac{25}{32}$ ", 1", $1\frac{1}{4}$ " $1\frac{3}{16}$ ", 2" (16mm, 20mm, 25mm, 32mm, 40mm, 51mm) arbor D5884, D5204 + D5511 arbor adaptor



D9599 INDUSTRIAL MAINTENANCE KIT
Contains holesaw sizes $\frac{3}{4}$ ", $\frac{7}{8}$ ", $1\frac{1}{8}$ ", $1\frac{3}{8}$ ", $1\frac{1}{2}$ ", $1\frac{3}{4}$ ", 2", $2\frac{1}{4}$ " (19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm) $2\frac{1}{2}$ ", 3", $3\frac{1}{4}$ ", $3\frac{3}{8}$ ", $3\frac{3}{4}$ ", $4\frac{1}{8}$ ", $4\frac{1}{2}$ " (64mm, 76mm, 83mm, 92mm, 95mm, 104mm, 114mm) arbors D5884, D5204 + D5511 arbor adaptor, $\frac{1}{4}$ " (6.5) pilot drill D8535 + D5500 12" extension


ACCESSORIES



5884B



5889B
Positive
Locking



5885B
Positive
Locking



5886B



5203BC



5201BC



5204BC
Quick
Change



5887B
Quick
Change



D5500 12" Extension




D5511
Arbor Adaptor

- D5500** 12" Extension fits all arbors except D5885 and D5887. Arbors D5809 and D5885 require extension adaptor D5502.
- D5511** Arbor adaptor - threaded adaptor and washer allows arbors D5884 and D5886 to be used with $\frac{1}{4}$ " to $1\frac{1}{2}$ " holesaws.
- D8534** $\frac{1}{4}$ " drill - short series use with D5889, D5885, D5203 arbors.
- D8535** $\frac{1}{4}$ " drill - long series - fits all Disston arbors except D5889, D5885 and D5203.
- D5506** Drive plate - used between holesaws and arbor recommended for light-medium torque applications - not recommended for 3" and over holesaws.
- SS1** Arbor set screw - for all arbors except D5204 and D5887.
- SS2** Arbor set screw - for arbors D5204 and D5887.

SIZES		PRODUCT NUMBER		PIPE SIZING		
DIAMETER INCHES	MM	SHOULDER BORES	DEPTH RIBS 500mm BARED	SHOULDER BORES	PIPE SIZE INCHES	PIPE SIZE MM
9/16	14	5855B				
5/8	16	5856B	5856C			
11/16	17	5857B				
3/4	19	5127B	5127C	5170C		
25/32	20	5888B	5888C			
13/16	21	5858B				
7/8	22	5128B	5128C	5890B	3/4	1 1/2
15/16	24	5859B				
1	25	5197B	5197C	5171C		
1 1/16	27	5860B				
1 1/8	29	5130B	5130C	5891B	1	3/4
1 3/16	30	5861B				
1 1/4	32	5131B	5131C	5172C		
1 5/16	33	5862B				
1 3/8	35	5132B	5132C	5892B		1
1 7/16	37	5863B				
1 1/2	38	5198B	5198C	5173C	1 1/4	
1 9/16	40	5864B				
1 5/8	41	5133B	5133C			
1 11/16	43	5865B				
1 3/4	44	5134B	5134C	5174C	1 1/2	1 1/4
1 15/16	46	5866B				
1 7/8	48	5135B	5135C			
2	51	5136B	5136C	5175C		1 1/2
2 1/16	52	5867B				
2 1/8	54	5199B	5199C			
2 1/4	57	5137B	5137C	5176C	2	
2 5/16	59	5868B				
2 3/8	60	5139B	5139C			
2 1/2	64	5138B	5138C	5177C		2
2 9/16	65	5869B				
2 5/8	67	5870B				
2 3/4	* 70	5871B				
2 7/8	73	5872B				
3	76	5150B	5150C	5893B		2 1/2
3 1/8	79	5873B				
3 1/4	83	5874B				
3 3/8	86	5875B				
3 1/2	89	5151B		5894B		
3 5/8	92	5876B			3 1/2	3
3 3/4	95	5877B				
3 7/8	98	5878B				
4	102	5152B				
4 1/8	105	5879B				
4 1/4	108	5880B		5895B		
4 3/8	111	5881B				
4 1/2	114	5153B				4
4 5/8	121	5882B			4 1/2	
5	127	5154B				
5 1/2	140	5155B			5	
5 3/4	146	5883B				
6	152	5156B				

* SOFFIT SIZE = 70mm 2 3/4"

Disston
PRO-Select



TOOLS OF THE TRADE LTD.,
Unit 14A, Harris Industrial Park, Stoke Prior, Bromsgrove, Worcestershire B60 4AE.
Telephone: 0527 579666, Fax: 0527 579644.

SOLE UK IMPORTERS FOR THE DISSTON COMPANY