



APC Displays+
01480 226600
sales@apc-displays.co.uk

12.1" Open Frame

Part No : HE121XAOT5
Item Description : 12.1" monitor / 5 wire resistive touch

Advantage and Application

- long term availability of adopted TFT LCD panels (stability of supply for min. 3 years)
- Analog RGB / DVI supportable
- 5 wire resistive touch adopted
- RS232 communication (option)
- Fine finishing metal chassis (brilliant design & complete set level OSD button)
- Application
 - Kiosks
 - ATMs
 - Casino & Amusement games
 - Lottery and Ticket sales
 - Self-Services
 - Industrial process control

Item	Description
Frame / bezel Color	EGL in black
Display Type	Size: 12.1" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
Active area	245.76 (H) x 184.32 (V)
Optimal (native) resolution	1024 x 768
Support color	16.2 M colors
Brightness (without touch)	550 cd/m2
Viewing Angles	80 / 80 / 80 / 80
Input video supportable	Analog RGB, DVI, Audio (option, 2W x 2W)
Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
Mounting Holes	VESA standard mounting 75 x 75 mm & 100 x 100 mm
Applicable Graphic Mode	VESA standard timing control
Weight & Volume	Unit Weight : 2,190 g, Carton Packing : pcs Carton weight : Kg

