


PMR209/P409, Film, Metallized Paper, Resistor/Capacitor, 0.22 uF, 20%, 630 V, 85C, Lead Spacing = 20.3mm



Dimensions	
L	24mm MAX
H	16.5mm MAX
T	11.3mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	150

General Information	
Supplier:	KEMET
Series:	PMR209/P409
Dielectric:	Metallized Paper
Style:	Radial
Features:	RC Unit approved
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	Resistor= 47 Ohms
Notes:	Not For New Design, Please Use The New P409 Series @ 275 VAC

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	20%
Voltage DC:	630 VDC
Voltage AC:	250 VAC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	3 GOhms
Safety Class:	X2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.