


Crimphousing 1,25 mm

Series

425



Rated current	1,0 A
Rated voltage	100 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for 1 minute
Material contact	Copper alloy
Material insulator	Thermoplast UL94V-0
Operating temperature	-40°C to +105°C

pitch
1,25

max.
pincount
015


All dimensions in mm.

Variation

Contact



Series

606





1

AWG 28 - 32



Section A-A



Section B-B

Plating:
T = Sn

Packaging:
R = Reel


Plating contact

Packaging

6	0	6	-	1	-	T	X	-	X	R
---	---	---	---	---	---	---	---	---	---	---

Crimp Tool

454



no. of contacts	see figure left	see figure left
n	A	B
002	4,25	1,25
003	5,50	2,50
004	6,75	3,75
005	8,00	5,00
006	9,25	6,25
007	10,50	7,50
008	11,75	8,75
009	13,00	10,00
010	14,25	11,25
011	15,50	12,50
012	16,75	13,75
013	18,00	15,00
014	19,25	16,25
015	20,50	17,50

4	5	4	-	1	-	0	1
---	---	---	---	---	---	---	---

Variation

No. of contacts



GARRY

www.mpe-connector.de

0000000000

Order code:

4 2 5 - 1 - ? ? ? - X - K S 0

Mating series	426	427
see page	3-10	3-11