

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0848548023

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

DeviceNet Micro-Change Single-Ended, 5 Poles, Male (Straight) to Pigtail, NMEA 2000 Style Cable, 2.0m (6.56') Length, meets NMEA 2000

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	84854
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	822350909143
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	146.963/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	22
Wire/Cable Type	Thin Standard Cable
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	NMEA-DND02NB-M020
Reference - Drawing Numbers	
Sales Drawing	SD-84854-018-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

84854 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION