





3F05-1



3L05-1



F6-1798 (1 per pack)

ADJUSTABLE SNAP DISC FAN & LIMIT CONTROLS

Adjustable Snap Disc Thermostat Allows You to Set the Temperature Set Point to Match Your Specific Needs Which Simplifies Inventory

FEATURES

- 1/4" quick connect terminals are standard.
- Reduces inventory while providing coverage for a wide range of temperature applications.
- Replaces the majority of fixed disc thermostats now on heating equipment and various appliances.
- 2 adjustable fan control models replace 7 fixed snap disc models.
- 5 adjustable limit control models replace 10 fixed snap disc models.

SPECIFICATIONS

ELECTRICAL RATINGS

VAC	Resistive (Non-Inductive)	Motor Rating (Inductive)		Pilot Duty
		Full Load	Locked Rotor	
120	25.0A	14.0A	72.0A	125 VA
240	25.0A	10.0A	60.0A	125 VA

PARTS AND ACCESSORIES

- F6-1798 Adapter plates (Order separately) — 1 per pack

Model Number	Temperature Range	Differential	Switch Action	Function	Accessories	Therm-O-Disc	
						Style	Type
3F05-1	90 to 130°F	20°F	SPST	Fan Controls	Includes thermostat and tab-to-screw terminals.	74T12	310708
3F05-2	140 to 180°F	20°F	SPST	(Close on Rise)		74T12	310709
3L05-1	135 to 175°F	40°F	SPST	Limit Controls		74T11	310710
3L05-2	175 to 215°F	40°F	SPST	(Open on Rise)		74T11	310711
3L05-3	210 to 250°F	40°F	SPST			74T11	310712
3L05-10	135 to 175°F	20°F	SPST			74T11	310724
3L05-13	250 to 290°F	40°F	SPST			74T11	310730