

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER 0G3B-0119-01	03JAN2002	EZ	DB



CLOGGED CAVITY

CLAMPING SCREW



284045-2 AS SHOWN



MATERIALS AND FINISH

HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.

CLAMP: BRASS, NICKEL PLATED.

DOUBLE SIDE CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.

CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2

WIRE SIZE RANGE:



12 - 30 AWG.



NOT CUMULATIVE TOLERANCE.




SELECTIVE GOLD PLATING, 0.00076 [0.00030]



RETENTION LATCH

6.25 REF

12.5



MATING FACE

POLARIZATION KEY SLOT

2.54 REF


2.54 REF

10.16±0.10

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±.3
2 PLC ±.25
3 PLC ±
4 PLC ±
ANGLES ±2

MATERIAL



FINISH



DWN 03JAN2002

E. ZANOLINI

CHK 03JAN2002

E. ZANOLINI

APVD 03JAN2002

D. BIEVENOUR

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics

Harrisburg, PA 17105-3608

NAME

TERMINAL BLOCK VERTICAL PLUG
STACKING LEFT HAND
10.16mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=284045

SCALE 3:1

SHEET

OF

1

REV

B