

M4/8.SFL

ABB contact for United
States of America

General Information

Extended Product Type:	M4/8.SFL
Product ID:	1SNA115661R2100
EAN:	3472591156614
Catalog Description:	M4/8.SFL Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator - Grey
Long Description:	M4/8.SFL Screw Clamp Terminal Blocks Fuse

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connecting Capacity-Main Circuit:	Screw Clamp / Rigid 1x 0.5 ... 6 mm ² Screw Clamp / Flexible 1x 0.5 ... 4 mm ²
Connection Type:	Screw clamp
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Fuse
Gauge Type:	A4
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Pollution Degree:	3
Product Main Type:	M4/8.SF
Product Name:	Terminal block
Rated Cross-Section:	4 mm ²
Rated Current (I_n):	Main Circuit 6.3 A
Rated Impulse Withstand Voltage (U_{imp}):	4000 V
Rated Voltage (U_r):	400 V
Recommended Screw Driver:	4 mm
RoHS Date:	20050818
Spacing:	8 mm
Sub-Function:	For 5x20 and 5x25 Fuses
Sub-Function 2:	With blown fuse indicator by Neon 110-230V
Sub-Function 3:	For 5x20 and 5x25 Fuses
Sub-Function 4:	With blown fuse indicator Neon
Wire Stripping Length:	9.5 mm

Certificates and Declarations (Document Number)

CSA Certificate:	TBD - OK in Ag.Base
cUL Certificate:	1SND161002A0202
Declaration of Conformity - CE:	1SND225007C1006
EAC Certificate:	1SND161009A1100
RoHS Information:	1SND230023F0206

Classifications

ETIM 4.0:	EC000899 - Fuse terminal block
ETIM 5.0:	EC000899 - Fuse terminal block
Object Classification Code:	X

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	101 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	265 mm
Package Level 1 Gross Weight:	0.70000 kg
Package Level 1 EAN:	3472591156614
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	6.200 kg
Package Level 3 Units:	21600 piece
Product Packing Type:	Box

Dimensions

Product Net Width:	8.0 mm
Product Net Height:	56.5 mm
Product Net Depth:	41.0 mm
Product Net Weight:	14.00 g

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Ordering

EAN:	3472591156614
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85361010

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity-Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 12 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 12 AWG

Flammability According to UL94: V0
