




PART NAME		NON-METALLIC ENCLOSURE (STYLE B)						PART No.		NBB-10245 & NBB-10265 & NBB-15245 & NBB-22245																	
MATERIAL:								FINISH:				INDUSTRY STANDARDS:															
UL LISTED INDOOR VERSION								BODY _____ LIGHT GRAY				UL LISTED INDOOR VERSION															
SOLID BODY & COVER _____ ABS/PC BLENDED PLASTIC								COVER _____ LIGHT GRAY OR CLEAR				UL508 TYPE 1, 2, 3, 3R, 4, 4X INDOOR, 12 & 13															
CLEAR COVER _____ POLYCARBONATE PLASTIC								LATCHES & HINGES _____ NON-METALLIC				NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13															
UL94-5VB FLAMMABILITY RATING								WALL MOUNTING BRACKETS _____ STAINLESS STEEL				IEC529-IP65															
UV STABILIZED																											
UL LISTED OUTDOOR VERSION												UL LISTED OUTDOOR VERSION															
SOLID BODY & COVER _____ PBT/PC BLENDED PLASTIC												UL508 TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13															
UL94-5VA FLAMMABILITY RATING												NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13															
UV STABILIZED												IEC529-IP65															
ABS VERSION												ABS VERSION															
SOLID BODY & COVER _____ ABS												NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13															
UL94-HB FLAMMABILITY RATING												IEC529-IP65															
ALL VERSIONS																											
GASKET _____ MODIFIED POLYURETHANE																											
NOTE: UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRKTS. & (4) M5 x 10mm LG. TRUSS HD. MACHINE SCREWS (NOT SHOWN)																											
COVER INCLUDES GRAY POLY-URETHANE GASKET.																											
INTERNAL HINGED PANEL MOUNTING BRACKETS, AIR & MOISTURE VENTS, STAINLESS STEEL LOCKING HASP AND GALVANIZED STEEL INTERNAL PANEL ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.																											
																											
0.575 [15] DIA. BOSS WITH 0.166 [4] DIA. HOLE x 0.395 [10] DEEP (4) PLACES								0.575 [15] DIA. BOSS WITH M5 x 0.8mm THREADED BRASS INSERT - (4) PLACES INSIDE (4) PLACES OUTSIDE																			
BOSSSES ACCEPT M5 METRIC OR #10 STD. SHEET METAL SCREWS x 0.375 [9] LG. (NOT SUPPLIED)																											
UL LISTED INDOOR VERSION		UL LISTED OUTDOOR VERSION		ABS VERSION		VIEW LESS COVER		DIMENSIONS = INCHES [MILLIMETERS]																			
PART NO.		PART NO.		PART NO.				NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED																			
SOLID COVER		CLEAR COVER		SOLID COVER		SOLID COVER		DIMENSIONS																			
A		B		C		D		E		F		G		H		J		K		L		M		N		P	
13.010		12.144		11.013		9.846		13.000		12.140		11.020		9.846		5.857		1.185		12.435		12.225		12.425		12.215	
[330]		[308]		[280]		[250]		[330]		[308]		[280]		[250]		[149]		[30]		[316]		[311]		[316]		[310]	
NBB-10245		NBB-10265		NBB-15245		NBB-22245																					