





REV.	DATE	DESCRIPTION
NC	08/03/98	INITIAL RELEASE
A	01/24/07	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	01/24/07						
7						CHECKED								
6						ISSUED				PART DESCRIPTION BNC CRIMP JACK – LMR200				
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1						PART NO. 112598				
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NICKEL	1						DWG. NO. 112598.DWG REV. A SIZE A SCALE NA				
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/112/112598.DWG							