





- OBSOLETE








-	-	-
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT
	PBT GLASS FIBER FILLED	FEMALE HOUSING
Q.TY	MATERIAL	DESCRIPTION
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY NO)	
G.14) PER ASSEMBLATO (QTY REQ'D PER ASSY) ELenco DEI COMPONENTI (PARTS LIST)		

GREEN	13/14	SELECTIVELY 1,3,4,6,8,9,10,11,12,13,14	14	32.5	37.4	5-284866-4	 15	1-2311508-4	5-2402732-4	 11					
BLUE		SELECTIVELY 1,3,4,6,11,12,13,14				1-284866-4	 15	2311508-4	 15	1-2402732-4					
-		SELECTIVELY 1,2,5,6,8,10,11,13				4-284866-3		-		4-2402732-3	 11				
-		SELECTIVELY 3,4,5,6,8,10,11,13				3-284866-3		-		3-2402732-3	 11				
-	2/3	SELECTIVELY 1,2,3,4,5,6,8,10,11,13	13	30.0	34.9	5-284866-3		-	5-2402732-3	 11					
BLUE		2/3				SELECTIVELY 1,3,4,6,7,9,11,12	12	27.5	32.4	1-284866-2	 15	2311508-2	1-2402732-2	 11	
BLACK		2/3				SELECTIVELY 1,3,5,6,7,8,9,10	10	22.5	27.4	2-284866-0			2-2402732-0		
BLUE		2/3				SELECTIVELY 1,2,3,4,5,6,7,8,10				1-284866-0	-	-			
-	2/3	SELECTIVELY 1,3,5,7,9		 15	9-2311507-9	-									
-	7/8	SELECTIVELY 1,2,4,6,8,9	2336596-9	-	-	 11									
GRAY	3/4	SELECTIVELY 1,3,4,6,8,9	9	20.0	24.9	7-284866-9	 15	8-2311507-9	7-2402732-9	 11					
RED	4/5	SELECTIVELY 1-2-4-6-8-9				8-284866-9	 15	7-2311507-9		8-2402732-9	 11				
-	2/3	SELECTIVELY 1,2,4,6,8,9				9-284866-9		/		9-2402732-9	 11				
GREEN		SELECTIVELY 1,2,4,6,7,9				1-284866-9	 15	6-2311507-9		1-2402732-9	 11				
BLACK		SELECTIVELY 1,3,5,7,8,9				6-284866-9	 15	5-2311507-9		6-2402732-9	 11				
ORANGE		SELECTIVELY 1,2,3,5,7,9				5-284866-9	 15	4-2311507-9		5-2402732-9	 11				
ORANGE		SELECTIVELY 1,3,4,6,8,9				4-284866-9	 15	3-2311507-9		4-2402732-9					
RED		SELECTIVELY 1,3,5,6,7,9				3-284866-9	 15	2-2311507-9		3-2402732-9	 11				
GREEN		SELECTIVELY 1,3,4,5,6,7,8,9				2-284866-9	 15	1-2311507-9		2-2402732-9	 11				
BLUE		SELECTIVELY 1,3,4,6,7,9				0-284866-9	 15	2311507-9		2402732-9	 11				
-		2/3				SELECTIVELY 1,3,5,6,8	8	17.5	22.4	6-284866-8		-	6-2402732-8		
-						SELECTIVELY 5,6,7				5-284866-8		-	5-2402732-8	 11	
BROWN						SELECTIVELY 1,2,3,4,6,8				4-284866-8	 15	3-2311507-8		4-2402732-8	
RED						SELECTIVELY 1,3,5,6,7,8				3-284866-8	 15	2-2311507-8		3-2402732-8	
GREEN			SELECTIVELY 1,3,4,5,6,7,8	2-284866-8	 15	1-2311507-8					2-2402732-8	 11			
BLUE	SELECTIVELY 1,3,4,6,7,8		0-284866-8	 15	2311507-8					2402732-8					
BLUE	2/3	SELECTIVELY 1,3,5,7	7	15.0	19.9	1-284866-7	 15	1-2311507-7	1-2402732-7						
BLUE	SELECTIVELY 1,3,5,6,7	0-284866-7				 15	2311507-7		2402732-7	 11					
-	4/5	SELECTIVELY 1,3,4,6	6	12.5	17.4	5-284866-6	 11	-	5-2402732-6						
BLACK	2/3	SELECTIVELY 1,3,4,6				4-284866-6	 15	2-2311507-6		4-2402732-6					
GREEN	4/5	SELECTIVELY 1,2,4,6				2-284866-6	 15	1-2311507-6		2-2402732-6					
BLUE	2/3	SELECTIVELY 1,3,5,6				0-284866-6	 15	2311507-6		2402732-6	 11				
-	2/3	SELECTIVELY 1,3,5	5	10.0	14.9	-	 15	4-2311507-5	-						
ORANGE	1/2	SELECTIVELY 3,4,5				4-284866-5	 15	3-2311507-5		4-2402732-5	 11				
GREEN		SELECTIVELY 1,2,3,5				3-284866-5	 15	2-2311507-5		3-2402732-5	 11				
BLUE		3/4				SELECTIVELY 1,3,4,5	2-284866-5	 15	1-2311507-5		2-2402732-5	 11			
RED	2/3	SELECTIVELY 2,4				0-284866-5	 15	2311507-5		2402732-5	 11				
GREEN	N/A	SELECTIVELY 1,2,4				4	7.5	12.4	2-284866-4	 15	2311507-4	2-2402732-4	 11		
GREEN	1/2	SELECTIVELY 1,3	3	5.0	9.9	2-284866-3	 15	1-2311507-3	2-2402732-3						
BLUE	-	SELECTIVELY 1,3				1-284866-3			1-2402732-3	 11					
BLUE	2/3	SELECTIVELY 1,3				0-284866-3	 15	2311507-3		2402732-3					
COLOUR CODE	 9	POLARIZ. RIB POS.	 5	CONTACT LOADING	HSG. POS.	DIM.A	DIM.B	TE P/N	 12	TE P/N	 13	TE P/N	 14		



-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS	03JUL2002	 TE Connectivity							
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2	DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES FINISH	v±0.2 ±0.1	APVD G. TURCO PRODUCT SPEC 108-20238 APPLICATION SPEC 114-18049-1	NAME	DUOPLUG 2.5 FEMALE CONN., SIDE LOCKING, KEYED (SELECTIVELY LOADED CONTACTS)					
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1												
Q.TY	MATERIAL	DESCRIPTION	ITEM								SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY INCL)			MATERIAL	SEE TABLE	SEE TABLE	CUSTOMER DRAWING	A1	00779	C=284866					
ELenco DEI COMPONENTI (PARTS LIST) G.T.Y. PER ASSEMBLATO (G.T.Y. FOR ASSY) P.T.Y. PER ASSY (P.T.Y. FOR ASSY)				SEE TABLE	-	SEE TABLE	CUSTOMER DRAWING	SCALE	10:1	SHEET	1	OF	5	REV D2	











(SCALE 4:1)






4805 (3/13)



D







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS	03JUL2002	TE Connectivity	
DIMENSIONS:		CHK -	-		
	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DUOPLUG 2.5 FEMALE CONN., SIDE LOCKING, KEYED (SELECTIVELY LOADED CONTACTS)	
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH	± ± ± ± ± ±°		
MATERIAL SEE TABLE		WEIGHT -		SIZE A 1	RESTRICTED TO -
-		CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO 284866
				SCALE 10:1	SHEET 5 OF 5
				REV 02	