




Telecommunication ADSL Transformer Transformers

DT32-2032AT
DT32-2065AT
DT32-2066AT
DT32-2028AT



DIMENSIONS IN mm

A	B	C	D	E	F	G
12.7 MAX.	2.79 MIN.	14.0 MAX.	14.0 MAX.	10.16±0.3	2.54±0.3	

ELECTRICAL CHARACTERISTICS				
	DT32-2032AT	DT32-2065AT	DT32-2066AT	DT32-2028AT
T.R	(PRI:SEC): 2:1±2% @10KHz 0.1V	(PRI:SEC): 2:1±2% @10KHz 0.1V	(PRI:SEC): 2:1±1% @10KHz 0.1V	(PRI:SEC): 1:1±1% @10KHz 0.1V
L	PRI: 410uH ± 5% @10KHz 0.1V	PRI: 409.5uH ± 5% @10KHz 0.1V	PRI: 409.5uH ± 5% @10KHz 0.1V	PRI: 470uH ± 5% @10KHz 0.1V
L.K	PRI: 6.5uH Max. @300KHz 0.1V	PRI: 6.5uH Max. @300KHz 0.1V	PRI: 6.5uH Max. @100KHz 0.1V	SEC: 10uH Max. @100KHz 0.1V
D.C.R	PRI: 0.6 Ω Max. N3: 0.2 Ω Max. N4: 0.2 Ω Max.	N1: 0.336 Ω Max. N2: 0.336 Ω Max. N3: 0.684 Ω Max. N4: 0.684 Ω Max.	N1: 0.6 Ω ±10% N2: 0.6 Ω ±10% N3: 0.15 Ω ±10% N4: 0.15 Ω ±10%	N1: 0.59 Ω ±10% N2: 0.59 Ω ±10% N3: 0.65 Ω ±10% N4: 0.65 Ω ±10%
HI-POT	1500 VAC 2 SEC	1500 VAC 2 SEC	1500 VAC 2 SEC	1500 VAC 2 SEC
C	-----	-----	-----	30pF Max. @10KHz 1V
I.L	1.0dB Max. @100KHz~300KHz	-----	-----	-----
L.B	40dB Min. @30KHz~300KHz	50dB Min. @20KHz~1MHz	46dB Min. @20KHz~1MHz	40dB Min. @20KHz~1MHz
FR	± 0.6dB @100KHz~200KHz	-----	-----	-----
R.L	-----	-----	-----	-----
T.H.D	-70dB Min. @20KHz	-----	-----	-----
Schematic	2	1	1	2

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.

TEL: 886-3-3626301 FAX: 886-3-3618901

http://www.deltaww.com