







Gecko Connectors

Cable Connectors – Individual Contacts

- ❖ 4-finger Beryllium Copper contact on a female connector.
- ❖ Ready for assembling to housings on page 8.
- ❖ Crimp barrel meets all crimp guidelines and standards.
- ❖ 2A current capacity, resists high vibration and shock.
- ❖ Withstands extremes of temperature: -65°C to +150°C.



GECKO

FEMALE SINGLE ENDED	FEMALE – FEMALE
	
MALE SINGLE ENDED	MALE – MALE
	
MALE – FEMALE	TOOLS
	Contact Insertion/Removal Tool – Z125-902 See page 12 ❖ Instruction sheets available at www.harwin.com/downloads/instructions

HOW TO ORDER

G125 - X WX XXXX X 94

SERIES CODE

GENDER – FIRST END

M	Male
F	Female

CABLE SIZE

W1	26 AWG
W2	28 AWG
W3	30 AWG
W4	32 AWG

CABLE COLOUR

94	White
-----------	-------

TERMINATION – SECOND END

L	Loose cut end
F	Female
M	Male

CABLE LENGTH

0150	150mm
0300	300mm (double-ended)
0450	450mm (single-ended)

All dimensions in mm.

Patent Pending – UK 1205109.0