










注記 NOTES

1. 使用材料 MATERIAL
 ハウジング HOUSING : LCP , UL94V-0
 アクチュエータ ACTUATOR : PA 46 , UL94V-0
 ターミナル : 青銅 (t=0.12) , 鎳・ビスマス (2%) , ニッケル下地
 TERMINAL : PHOSPHOR BRONZE , TIN- 2% BISMUTH OVER NICKEL PLATING.
 金具 : 青銅 (t=0.2) , 鎳・ビスマス (2%) , ニッケル下地
 STOPPER : PHOSPHOR BRONZE , TIN OVER NICKEL PLATING.
- △ ソルダータール半田付け面のスレ量は、基準値 R に対し、
 上方0MAX、下方0。1MAX とする。
 又、相互のバラツキ量は、0.1MAX とする。
 MISALIGNMENT OF SOLDER TAILS AND FITTING NAILS FROM R
 UPPER DIRECTION : 0 MAX, LOWER DIRECTION : 0.1 MAX.
 OFFSET BETWEEN SOLDER TAILS AND FITTING NAILS : 0.1 MAX.
3. 一般公差 : ±0.3
 GENERAL TOLERANCES : ±0.3
4. 本製品は54809-***27の鉛フリー品である。
 THIS PRODUCT IS LEAD FREE OF 54809-***27



12.0	11.4	10.8	14.0	54809-3998	54809-3928	39
D	C	B	A	EMBOSSSED TAPE	MATERIAL NO.	CKT.
				ORDER No. オーダー番号		

54809-**28	MODEL NO.
------------	-----------

DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
------------------------	---

REVISED EC NO.: J2014-1896 DRAWN: AYOSHI I01 2014/06/30 CHKD: YKOBAYASHI 022014/06/30 APPR: YNOGAWA 2014/07/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	± ---	DRAWN BY M. NABEI	DATE '03/12/22	TITLE 0.3 FPC CONN E/O HSG ASSY (H=1.3) -LEAD FREE-		
		10 OVER 30 UNDER	± ---	CHECKED BY K. TOJO	DATE '03/12/22			
		30 OVER	± ---	APPROVED BY M. SASAO	DATE '03/12/22			
		ANGULAR ± --- °		MATERIAL NO.				
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

10

9

8

7

6

5

4


3

2


1

引き出し方向

PULL OUT




"F"



DETAIL "F"

注記 NOTES


- 製品詳細寸法については、図面SD-54809-036を参照下さい。
RE DETAILED DIMENSION, SEE SD-54809-036.
- 梱包数量: 2500個/リール
NUMBER OF CONNECTORS : 2500PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度: 0.1 ~ 1.3N (10 ~ 130gf)

(剥離方向は下図参照)

尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1 ~ 1.3N (10 ~ 130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.



- 材料 (MATERIAL)
キャリアテープ (CARRIER TAPE): ポリプロピレン (POLYPROPYLENE)
トップテープ (TOP TAPE): PET, PE, PEF
リール (REEL): ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>
- 本製品は54809-**-91の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54809-**-91

REVISED EC NO: J2014-1896 DRWN:AYOSHI I 01 2014/07/01 CHKD:YKOBAYASHI 022014/06/30 APPR: YNOGAWA 2014/07/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	M. NABEI	'03/12/22	TITLE EMBSTP PKG FOR 0.3 FPC CONN E/O -LEAD FREE- molex				
		10 OVER 30 UNDER	± ---	CHECKED BY K. TOJO	'03/12/22					
		30 OVER	± ---	APPROVED BY M. SASAO	'03/12/22					
		ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-54809-037		1 OF 4			
D	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9

8

7

6

5

4

3

2

10

9

8

7

6

5

4

3

2

1

F

E

D

C

B

A

F




E

D

C

B

A



1 6mm幅キャリアテープ
16mm WIDTH CARRIER TAPE

REVISED EC NO: J2014-1896 DRWN:AYOSHI I 01 2014/06/30 CHKD:YKOBAYASHI 022014/06/30 APPR:YNOGAWA 2014/07/17	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± ---	DRAWN BY M. NABEI	DATE '03/12/22	TITLE EMBSTP PKG FOR 0.3 FPC CONN E/O -LEAD FREE- molex			
		10 OVER 30 UNDER	± ---	CHECKED BY K. TOJO	DATE '03/12/22				
		30 OVER	± ---	APPROVED BY M. SASAO	DATE '03/12/22	DOCUMENT NO. SD-54809-037			
		ANGULAR ± --- °		MATERIAL NO. SEE TABLE					
D		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9

8

7

6

5

4

3

2

10

9

8

7

6

5

4

3

2

1

F


E

D

C

B

A



24	29.4	25.4	11.6	12.3	14.2	54809-3998	39
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	C	B	A	MATERIAL NO.	極数 CKT.

REVISED EC NO: J2014-1896 DRWN:AYOSHI I 01 2014/06/30 CHKD:YKOBAYASHI 022014/06/30 APPR:YNOGAWA 2014/07/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY M.NABE I	DATE '03/12/22	TITLE EMBSTP PKG FOR 0.3 FPC CONN E/O -LEAD FREE- molex				
		10 OVER 30 UNDER	± ---	CHECKED BY K.TOJO	DATE '03/12/22					
		30 OVER	± ---	APPROVED BY M.SASAO	DATE '03/12/22					
		ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-54809-037		3 OF 4			
	REV			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9

8

7


6

5

4

3

2



32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE

REVISED EC NO: J2014-1896 DRWN:AYOSHI I01 2014/06/30 CHKD:YKOBAYASHI 022014/06/30 APPR:YNOGAWA 2014/07/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
		10 UNDER	± ---	DRAWN BY M.NABEI	DATE '03/12/22	TITLE EMBSTP PKG FOR 0.3 FPC CONN E/O -LEAD FREE-					
		10 OVER 30 UNDER	± ---	CHECKED BY K.TOJO	DATE '03/12/22						
		30 OVER	± ---	APPROVED BY M.SASAO	DATE '03/12/22	molex					
	ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.					SHEET NO.	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-54809-037		4 OF 4				
D	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						