


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1116	B	Drawing was CRS-TO-****	JWM	6/13/01	JC	6/20/01	JC	6/20/01
1369	C	Bulk items added	JWM	12/10/02	JC	2/19/02	JC	2/19/03



NOTES:

1. Electro-plated Copper
2. Voltage Rating: 600V

SPC Type No.	Pkg. Qty	Wire Range (AWG)	Stud Size	L	W	E	C	S	T	Thickness
CRS-TO-1006	50	12 ~ 10	6	.68	.28	.54	.29	.143	.135	.040
SPC3731	500		8	.68	.28	.54	.29	.174		
CRS-TO-1008	50		10	.73	.38	.54	.29	.200		
SPC3732	500		1/4	.96	.53	.69	.44	.264		
CRS-TO-1010	50		5/16	.96	.53	.69	.44	.328		
SPC3733	500		3/8	.96	.54	.69	.44	.390		
CRS-TO-1025	50									
SPC3734	500									
CRS-TO-1031	50	16 ~ 14	6	.60	.25	.47	.22	.148	.090	
SPC3735	500		8	.74	.31	.58	.33	.174		
CRS-TO-1037	50		10	.74	.31	.58	.33	.200		
SPC3736	500		1/4	.89	.47	.65	.40	.265		
CRS-TO-1406	100	22 ~ 18	2	.60	.25	.48	.23	.088	.070	.030
SPC3727	1000		4	.60	.25	.47	.22	.118		
CRS-TO-1408	100		6	.60	.25	.47	.22	.144		
SPC3728	1000		8	.74	.31	.58	.33	.174		
CRS-TO-1410	100		10	.74	.31	.58	.33	.195		
SPC3729	1000		1/4	.88	.47	.65	.40	.265		
CRS-TO-1425	100									
SPC3730	1000									
CRS-TO-1802	100	26 ~ 24	0	.32	.14	.24	.11	.060	.030	.020
SPC3721	1000		2	.31	.14	.24	.11	.090		
CRS-TO-1804	100		4	.45	.20	.35	.21	.116		
SPC3722	1000		6	.45	.20	.35	.21	.143		
CRS-TO-1806	100									
SPC3723	1000									
CRS-TO-1808	100									
SPC3724	1000									
CRS-TO-1810	100									
SPC3725	1000									
CRS-TO-1825	100									
SPC3726	1000									
CRS-TO-2200	100									
SPC3717	1000									
CRS-TO-2202	100									
SPC3718	1000									
CRS-TO-2204	100									
SPC3719	1000									
CRS-TO-2206	100									
SPC3720	1000									

SPC-F004.DWG

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
JC	3/1/91
CHECKED BY:	DATE:
JOHN COLE	11/21/91
APPROVED BY:	DATE:
Jliska	11/21/91

DRAWING TITLE:

Non-Insulated Ring Tongue Terminals

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-354	TA-354.dwg	C
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1