

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0524921320
Status: Planned for Obsolescence
Description: 1.25mm (.049") Bottom Entry Receptacle, 13 Circuits

Documents:

3D Model Product Specification PS-52492-001 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)

General

Product Family FFC/FPC Connectors
Series 52492
Product Name N/A

Physical

Circuits (Loaded) 13
Color - Resin Natural
Contact Position N/A
Entry Angle Bottom Entry
Mated Height 5.90mm (.232")
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Number of Rows 1
Orientation Bottom Entry
PC Tail Length 3.20mm (.126")
PCB Retention None
Packaging Type Tray
Pitch - Mating Interface 1.25mm (.049")
Plating min - Mating 0.914µm (36µ")
Plating min - Termination 0.914µm (36µ")
Polarized to PCB Yes
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +85°C
Termination Interface: Style Through Hole - Kinked Pin
Wire/Cable Type FFC/FPC

Electrical

Current - Maximum per Contact 0.5A, 1A
Voltage - Maximum 200V

Material Info

Reference - Drawing Numbers

Product Specification PS-52492-001, RPS-52492-001, RPS-52492-002,
RPS-52492-003
Sales Drawing SD-52492-**20

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

52492Series