

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —, *

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

NOTES:


Tolerances cable lengths:

0m to 0.5m	+30mm
------------	-------


0.5m to 1.0m	+50mm
--------------	-------

1.0m to 3.0m	+100mm
--------------	--------

< 3.0m +1.5%



VIEW 'A'




PVC CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (moving)	15 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APV
	A	INITIAL RELEASE	26NOV2013	GSK	BvH
	A1	ECR-14-015049	13OCT2014	GSK	BvH
	A2	ECR-16-003945	16MAR2016	GSK	BvH

TECHNICAL DATA		Temperature range (mobile) –
Operating voltage	max. 60 V AC/DC	
Operating current per contact	max. 4 A	
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing	
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)	

PUR CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
C-track properties	
Jacket	PUR/PVC (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (moving)	15 x outer diameter
Temperature range (fixed)	−30...+80 °C
Temperature range (mobile)	−5...+70 °C

4 pos	10mtr	PVC	Grey	1-2273099-4	4x22AWG PVC 10.0m	8
	5mtr			1-2273099-3	4x22AWG PVC 5.0m	7
	3mtr			1-2273099-2	4x22AWG PVC 3.0m	6
	1.5mtr			1-2273099-1	4x22AWG PVC 1.5m	5
4 pos	10mtr	PUR	Grey	2273099-4	4x22AWG PUR 10.0m	4
	5mtr			2273099-3	4x22AWG PUR 5.0m	3
	3mtr			2273099-2	4x22AWG PUR 3.0m	2
	1.5mtr			2273099-1	4x22AWG PUR 1.5m	1
	LENGTH"L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR.G CHK B.VELDHOVEN APVD A.VAN ZANDVOORT PRODUCT SPEC 108-19483 APPLICATION SPEC 114-32127 WEIGHT		TE Connectivity NAME M12 X 1.0 ANGLED SOCKET PIGT SHLD A			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:			SIZE	CAGE CODE	DRAWING NO	RESTRICTED T
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			A3	00779	C-2273099	—
MATERIAL —	FINISH —	CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A2