

SPECIFICATIONS**Mechanical**

Plug Mating Force: 3.00kg (6.61Lb) max.
Plug Unmating Force: 0.40~3.00kg (0.88~6.61Lb)
Contact Retention Force: 0.50kg (1.10Lb) min.
Durability: 5000 Cycles

Electrical





Current Rating: 1.00A
Contact Resistance: 50mΩ max.
Dielectric Withstanding Voltage: 500V AC/1min min.
Insulation Resistance: 100MΩ min.

Physical

Housing: Thermoplastic, UL 94V-0 rated
Contact: Copper alloy
Plating: See "ORDERING INFORMATION"
Operating Temperature: -25°C to +85°C
Recommended Thickness of PCB: 1.60[.063]

Audio Jack Connector**JA Series**

Triple Jack, R/A, T/H Type
3.5mm [.138"]
13 Pos.

**DRAWING**RECOMMENDED P.C.B. LAYOUT**ORDERING INFORMATION**

PRODUCT NO.: JA 3 3 3 3 * - H23P - 4F

Audio Jack Series _____
 Body Type _____
 3-Triple Jack
 Sleeve Style _____
 3-All Plastic Cylindrical
 Plug Type _____
 3-Triple Band
 Plug Diameter _____
 3-3.50mm

Lead Free Code _____
 Extension Code _____
 Contact Area Plating
 1-Gold Flash
 F-Gold Flash (Lead Free)