


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)												
PLP1S	.06 (1.5)	1.00 (25.4)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	5.3 (135)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.24 (109)
PLP1.5S	.06 (1.5)	1.50 (38.1)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	6.7 (170)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.29 (132)
PLP2S	.06 (1.5)	1.75 (44.5)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	7.88 (200)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.32 (145)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

2) SEE DRAWING SS-26888(A) FOR PLP1.5I.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE							
							STRAP, PUSH MOUNT-PLP							
							CUSTOMER DRAWING							
							ITEM REVISION NAME			PANDUIT				
							SS-26803/AB							
							DATASET FILE NAME							
							SS-26803_DC/AB SS-26803_REV07							
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						MATERIAL:	
							.x ± .1 [2.5] .xxx ± .020 [.51]						NYLON 6.6	
							.xx ± .02 [.5] ANGLES ± - - - -							
							- THIRD ANGLE PROJECTION						DRAWING NUMBER:	
													SS - 26803	
07	11/04/14	BWG	MPH	JADE	CHANGED "B" DIMENSION TO .190 AND UPDATED TITLE BORDER AND NOTES. SEE ECN FOR COMPLETE DETAILS.	SS-26803/07	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1		SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	RAM		4/27/93	HVP	NONE			A