

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL

94V-0

Contact Plating: TiN, 80-100μ”

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V





Insulator Resistance: 1000MΩ

Min.

Operating Temp.: -40℃~+105℃

NUMBER OF POSITIONS	DIMENSIONS	
	A	B

06	2.54	18.31
08	3.81	19.58
10	5.08	20.85
12	6.35	22.12
14	7.62	23.39
16	8.89	24.66
18	10.16	25.93
20	11.42	27.20
24	13.97	29.74
26	15.24	31.01
30	17.78	33.55
34	20.32	36.09
40	24.13	39.90
50	30.48	46.25
60	36.83	52.60
64	39.37	55.14



P.C.B LAYOUT

UNLESS TOLERANCE		DRAW BY		CnC Tech,LLC		
GENERAL	ANGLE	DESIGN BY				
X. ± 0.30°	X.° ± 3.0°	CHECK BY				
.X ± 0.20	.X° ± 2.0°	APPROVE BY				
.XX ± 0.15	.XX° ± 1.0°			Part No. 3210-XX-002-11-99		
.XXX ± 0.08	.XXX ± 0.5°					
		SCALE	SHEET	UNIT	DRAW NO:	
		1:1	1/1	MM		
						REV: A