




**Models 6856, 6857
XLR (F/F), XLR (M/M)***Model 6856 XLR (F/F) Adapter**Model 6857 XLR (M/M) Adapter*

Pomona XLR adapters are ideal for your audio applications.

Features

- Sleek light weight design.
- 3-pin XLR-to-XLR adapters.
- Tarnish-resistant.

Materials

- Body is die cast zinc alloy with tarnish resistant nickel plating.
- Male pin contacts are nickel-plated brass.
- Female contacts are nickel-plated beryllium copper.

Ordering Information

Model: 6856, 6857

Specifications

Number of Contacts	3
Contact Resistance	$\leq 3 \text{ m}\Omega$
Dielectric Strength	1000 V dc

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Last Update: 10/1/07
D1104274, Rev. 002

Page 1 of 1